


LOC		DIST		P		F		ZONE		LTR		REVISIONS		DATE		APPD	
AF		50								5		REV PER 0G3A-0403-01		28 Jun 01		JR/DD	

- 1 CONTINUOUS STRIP ON REELS
2 PRE-PLATE .000100 MIN TIN OVER
.000050 MIN NICKEL, POST PLATE
.000080 MIN TIN PER MIL-T-10727
3 .000080 MIN TIN PL PER MIL-T-10727.
4 WITH INTERLEAVING PAPER.
5 PRELIMINARY - NOT FOR PRODUCTION.



SECTION A-A
SCALE 10:1

SECTION B-B
SCALE 10:1

4M BRASS	3			4/5	60799-6
4M BRASS	3				60799-5
PHOS BRONZE	2				60799-4
4M BRASS					60799-2
MATERIAL	FINISH	INSULATION DIA	WIRE RANGE	PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± .015 ANGLES ± 1°		DR 12/13/88 P FORTNEY CHK 6/14/89 MS FEHER APPD 6/14/89 G YETTER APPD 6/14/89 R KUZO PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		AMP AMP INCORPORATED Harrisburg, Pa. 17105	
SEE TABLE		.090-.125		18-14	
SEE TABLE		NAME		RECEPTACLE, SHUR PLUG, .180 DIA	
SIZE		FSCM NO	DRAWING NO		
C		00779	60799		
SCALE		5:1	SHEET	1 OF 1	

F OR O	.140	.210	F	.100	.077	14
				.067	16	
				.061	18	
TYPE	WIDTH	STRIP LENGTH ±.015	TYPE	WIDTH	±.002 HEIGHT	WIRE
INSUL BARREL CRIMP			WIRE BARREL CRIMP			