

HALF SIZE DIP LOW VOLTAGE 5.0V CRYSTAL CLOCK OSCILLATOR

ACH Series



ESD Sensitive



RoHS/RoHS II Compliant



12.7 x 12.7 x 5.6mm

Moisture Sensitivity Level (MSL) – This product is Hermetically Sealed and not Moisture Sensitive - MSL = N/A: Not Applicable

FEATURES:

- Wide frequency range.
- HCMOS and TTL compatible.
- Tight symmetry option.
- Tri-state Enable / Disable function.

APPLICATIONS:

- Microprocessors.
- Digital circuit.

STANDARD SPECIFICATIONS:

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range		0.032768		200.000	MHz	
Operating Temperature		0		+70	°C	See options
Storage Temperature		-55		+125	°C	
Overall Frequency Stability		-100		+100	ppm	See options
Supply Voltage (Vdd)		4.5	5.0	5.5	V	
Input Current	32.768kHz ~ 23.999MHz			30	mA	
	24.000MHz ~ 49.999MHz			45		
	50.000MHz ~ 79.999MHz			70		
	80.000MHz ~ 200.999MHz			85		
Symmetry (@ 1/2Vdd)	32.768kHz ~ 49.999MHz	45		55	%	See options
	50.000MHz ~ 200.000MHz	40		60		
Rise and Fall Time (Tr/Tf)	32.768kHz ~ 1.999MHz			40	ns	
	2.000MHz ~ 24.000MHz			10		
	24.001MHz ~ 200.000MHz			5		
Output Load	32.768kHz ~ 79.999MHz			15	pF	See options
				10	TTL	
	15			pF		
	5			TTL		
Output Voltage		VOH	0.9*Vdd		V	
		VOL		0.1*Vdd	V	
Tri-state Function		VIH	2.2		V	"1" or Open: Oscillation
		VIL			0.8	V
Output Enable time				4	ms	For option A only
Output Disable time				100	ns	For option A only
Start-up Time			1	10	ms	

* Overall frequency stability includes initial tolerance and temperature stability.

HALF SIZE DIP LOW VOLTAGE 5.0V CRYSTAL CLOCK OSCILLATOR

ACH Series


 RoHS/RoHS II Compliant




12.7 x 12.7 x 5.6mm

OPTIONS & PART IDENTIFICATION:

(Left blank if standard)



OUTLINE DIMENSION:



Pin	Function
1	Tri-State/NC
4	Case GND
5	Output
8	Vdd

Dimensions: inches (mm)

Packaging: 40pcs /tube

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS
ISO9001:2008
CERTIFIED

 **ABRACON**[®]
The Power of Linking Together LLC

2 Faraday, Suite# B | Irvine | CA 92618 Revised: 09.24.15
Ph. 949.546.8000 | Fax. 949.546.8001
Visit www.abracon.com for Terms and Conditions of Sale

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ACH-48.000MHZ-EK](#) [ACH-40.000MHZ-EK](#) [ACH-12.000MHZ-EK](#) [ACH-4.000MHZ-EK](#) [ACH-50.000MHZ-EK](#) [ACH-27.000MHZ-EK](#) [ACH-14.31818MHZ-EK](#) [ACH-16.000MHZ-EK](#) [ACH-25.000MHZ-EK](#) [ACH-24.576MHZ-EK](#) [ACH-10.000MHZ-EK](#) [ACH-18.432MHZ-EK](#) [ACH-20.000MHZ-EK](#) [ACH-32.000MHZ-EK](#) [ACH-32.768MHZ-EK](#) [ACH-8.000MHZ-EK](#) [ACH-3.6864MHZ-EK](#) [ACH-11.0592MHZ-EK](#) [ACH-2.5600MHZ-L-A](#)