







注記 NOTES


- 1. 製品詳細寸法については図面5047541000を参照下さい。
REFER TO THE 5047541000 ABOUT DIMENSIONS IN DETAIL.
- 2. 梱包数量：5000個/リール
NUMBER OF CONNECTORS：5000 PCS/REEL
- 3. リードテープ長さ
LEAD TAPE LENGTH



- 4. 材料 MATERIAL
キャリアテープ(CARRIER TAPE)：ポリスチレン(POLYSTYRENE)
トップテープ(TOP TAPE)：PET, PE, PEF
リール(REEL)：ポリスチレン(PS)リサイクル材含む
POLYSTYRENE(PS)RECYCLE MATERIAL CONTAINED
- 5. ELV及びRoHS適合品
ELV AND RoHS COMPLIANCT




THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
REVISED	EC NO: 106328 DRWN: YCHEN128 CHK'D: YKOBAYASHI02 APPR: TKUSUHARA01	2016/07/05 2016/07/07 2016/07/07	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE	molex®									
					MM	40:1										
			ANGULAR TOL ± 1.0 °		DRWN BY		DATE		0.3 FPC CONN. B/F LA75 SERIES TAPING PKG							
					AYOSHII01		2016/03/18									
			4 PLACES ± 0.03		CHK'D BY		DATE									
					YKOBAYASHI02		2016/03/31									
			3 PLACES ± 0.03		APPR BY		DATE		PRODUCT CUSTOMER DRAWING							
					TKUSUHARA01		2016/03/31									
			2 PLACES ± 0.05		DRAWING SIZE	THIRD ANGLE PROJECTION		504754		SEE CHART		CUSTOMER				
					A3											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER								
										B		REV		5047540000		PSD





32±0.3	28.4	14.2	33.4	20.0	504754-6100	61
				17.0	504754-5100	51
24±0.3	--	11.5	25.4	14.0	504754-4100	41
				13.4	504754-3900	39
				12.8	504754-3700	37
				12.2	504754-3500	35
				11.6	504754-3300	33
				11.0	504754-3100	31
				9.2	504754-2500	25
				8.0	504754-2100	21
16±0.3	--	7.5	17.4	6.5	504754-1600	16
				6.2	504754-1500	15
				4.9	504754-1100	11
				4.3	504754-0900	9
				3.7	504754-0700	7
Eキャリアテープ幅 EMBOSSED TAPE WIDTH	D	C	B	A	オーダー番号 ORDER NO.	極数 CIRCUITS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

REVISED	EC NO: 106328	2016/07/05	APPR: TKUSUHARA01	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE	molex®							
	DRWN: YCHEN128	2016/07/07				MM	10:1								
	CHK'D: YKOBAYASHI02	2016/07/07		ANGULAR TOL ± 1.0 °		DRWN BY		DATE		0.3 FPC CONN. B/F LA75 SERIES TAPING PKG					
				4 PLACES	± 0.03	AYOSHII01		2016/03/18							
				3 PLACES	± 0.03	CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING					
				2 PLACES	± 0.05	YKOBAYASHI02		2016/03/31							
				1 PLACE	± 0.1	APPR BY		DATE		SERIES		MATERIAL NUMBER		CUSTOMER	
				0 PLACES	± 0.2	TKUSUHARA01		2016/03/31							
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE	THIRD ANGLE PROJECTION		504754		SEE CHART				
						A3									
B	REV							DOCUMENT NUMBER		DOC TYPE	DOC PART	SHEET NUMBER			
								5047540000		PSD	000	2 OF 2			

RELEASE STATUS	P1	RELEASE DATE	07.07.2016	08:34:58
----------------	----	--------------	------------	----------





推奨基板レイアウト
RECOMMENDED P.C. BOARD
PATTERN LAYOUT

推奨メタルマスク厚さ : 0.1mm
RECOMMENDED METAL MASK THICKNESS : 0.1mm


推奨開口率 : 80%
APERTURE RATE : 80%

注記
NOTE


1. 必ず基板に実装してからアクチュエ-タを操作して下さい。
PLEASE OPERATE THE ACTUATOR AFTER MOUNTING ON THE SUBSTRATE.

2. FPCについて
ABOUT FPC
補強フィルム材質はポリイミドを推奨します。ベースフィルムは25μmを推奨します。
接着剤は熱硬化接着剤を推奨します。
尚、接着剤の接点部への付着は導通不良の原因になりますので、染み出しが無い様、お願い致します。
RECOMMENDED STIFFENER MATERIAL: POLYIMIDE
RECOMMENDED BASE FILM THICKNESS: 25 MICROMETER
RECOMMENDED ADHESIVE: THERMOSETTING ADHESIVE
NOTE: PLEASE PUT APPROPRIATE AMOUNT OF ADHESIVE ON ADHEREND BECAUSE THERE IS A POSSIBILITY THAT THE EXTRA ADHESIVE CAUSES THE DEFECT IN ELECTRICAL CONTINUITY.

打抜き方向は導体側から補強板側を推奨致します。
RECOMMENDED PUNCHER DIRECTION:
FROM CONDUCTOR SIDE TO STIFFENER FILM SIDE.



FPC構成推奨仕様
STRUCTURE OF FPC



適合金メッキFPC推奨寸法
仕上がり厚さ : 0.2 ±0.03
APPLICABLE FPC WITH GOLD PLATING
RECOMMENDED DIMENSION
THICKNESS : 0.2 ±0.03

