

THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION

19


BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
CM	53	P	LTR	DESCRIPTION	DATE	DWN	APVD
			N	REACTIVATED -1 PER PR CM 94-73	7-25-94	KS	RS
				REV & REDWN PER EC 0730-0121-94			

1. PARTS MUST COMPLY WITH AMP SOLDERABILITY SPECIFICATION 109-11-3.
2. DIMENSIONS IN BRACKETS ARE IN INCHES.



RECOMMENDED P.C. BOARD LAYOUT
FOR 3.18 [0.125] THICK P.C. BOARD
SCALE 10:1



SECTION A-A

METRIC

COPPER ALLOY, PRE-TIN		NYLON 6/6, NATURAL		350542-1	
PIN CONTACT MATERIAL & FINISH		HOUSING MATERIAL & COLOR		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN	7-25-94	AMP AMP Incorporated Harrisburg, PA 17105-3608	
		CHK	7-25-94		
DIMENSIONS: mm [INCHES]		APVD	7-28-94	NAME HEADER ASSEMBLY, 3 CIRCUIT, COMMERCIAL MATE-N-LOK	
		PRODUCT SPEC			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.13 [0.005] 3 PLC ±- 4 PLC ±- ANGLES ±0°30' FINISH SEE TABLE		APPLICATION SPEC		SIZE A2	
		WEIGHT	-		
MATERIAL SEE TABLE		CUSTOMER DRAWING		CAGE CODE 00779	DRAWING NO C=350542
				SCALE 5:1	SHEET 1 OF 1
				REV N	