




.050" [1.27 mm] Contact Centers, .610" [15.49 mm] Insulator Height,
Dip Solder/Card Extender/SMT for .031" [0.79 mm], .062" [1.57 mm] or .093" [2.36 mm] Mating PCB





SPECIFICATIONS

- Accommodates .031" $\pm$.006" [0.79 mm $\pm$ 0.15 mm], .062" $\pm$.008" [1.57 mm $\pm$ 0.20 mm] or .093" $\pm$.008" [2.36 mm $\pm$ 0.20 mm] mating PCB
- PPS or PA9T insulator
- Molded-in key available
- High reliability/high cycle hairpin bellow & cantilever contacts
- 1 Amp current rating per contact for contacts fully energized
- UL Flammability Rating: 94V-0
- Operating Temperature: -65°C up to +200°C




TERMINATION TYPE

HAIR PIN POST .018" [0.46] X .012" [0.30]	(P/N CODE) TERMINATION LAYOUT	ROW SPACING (R' DIM)	TAIL LENGTH (L' DIM)
	(HH) THRU HOLE STRAIGHT figure 1	3 X 0.100" [2.54]	0.125" [3.18]
	(HR) CARD EXTENDER figure 2	ACCEPTS .062" [1.57] PCB	0.160" [4.06]
	(HF) SURFACE MOUNT figure 3	N/A	0.100" [2.54]
	(HL) THRU HOLE STRAIGHT figure 4	0.250" [6.35]	0.160" [4.06]
	(HN) THRU HOLE STRAIGHT figure 4	0.100" [2.54]	0.125" [3.18]
CANTILEVER POST SIZE .016" [0.41] SQ.	(P/N CODE) TERMINATION LAYOUT	ROW SPACING (R' DIM)	TAIL LENGTH (L' DIM)
	(YH) THRU HOLE STRAIGHT figure 1	3 X 0.100" [2.54]	0.125" [3.18]
	(YR) CARD EXTENDER figure 2	ACCEPTS .062" [1.57] PCB	0.175" [4.45]
	(YF) SURFACE MOUNT figure 3	N/A	0.100" [2.54]
	(YS) THRU HOLE STRAIGHT figure 4	0.200" [5.08]	0.140" [3.56]




MOUNTING STYLE




BOARD LOCK (R)
(with no mounting ears)




NO MOUNTING EARS (N)



FLUSH MOUNTING (D)



**FLUSH MOUNTING
WITH THREADED INSERT (T)**



STRADDLE MOUNT (Q)

