

Low Pass Filter

75Ω DC to 32 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Pin Connections




INPUT	1
OUTPUT	8
GROUND	2,3,4,5,6,7
CASE GROUND	2,3,4,5,6,7
DEMO BOARD	TB-305

Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F
.770	.800	.385	.400	.370	.400
19.56	20.32	9.78	10.16	9.40	10.16
G	H	J	K	wt	
.200	.20	.14	.031	grams	
5.08	5.08	3.56	0.79	5.2	




Features

- rugged welded case, hermetic
- other standard and custom PLP models available with wide selection of fco

Applications

- test equipment
- lab use
- transmitters/receivers
- military/hi-rel applications



CASE STYLE: A01
PRICE: \$15.20 ea. QTY (1-9)


+ RoHS compliant in accordance with EU Directive (2002/95/EC)

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications.

Low Pass Filter Electrical Specifications

PASSBAND (MHz)	fco (MHz) Nom.	STOPBAND (MHz)	VSWR (:1)
(loss < 1 dB)	(loss 3 dB)	(loss > 20 dB) (loss > 40 dB)	Passband Typ. Stopband Typ.
DC-32	35	47-61 61-200	1.7 18

typical frequency response



electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
	$\bar{x}$	σ		
1.00	0.03	0.00	1.00	26.18
5.30	0.07	0.01	1.17	27.11
9.50	0.11	0.00	1.35	25.77
13.80	0.12	0.00	1.56	23.82
18.00	0.17	0.01	1.81	25.02
22.30	0.23	0.01	2.09	25.16
26.50	0.29	0.02	2.42	25.16
32.00	0.71	0.12	2.80	23.94
35.00	2.88	0.37	3.25	23.99
38.00	8.19	0.35	3.73	25.10
39.80	12.12	0.33	4.31	24.36
41.60	16.01	0.34	4.95	24.94
43.40	19.70	0.36	5.73	24.71
45.20	23.14	0.38	6.58	24.62
47.00	26.35	0.40	7.62	24.85
48.80	29.36	0.40	8.75	24.95
51.20	33.07	0.40	10.13	25.02
53.70	36.65	0.39	11.63	25.78
56.10	39.87	0.40	13.46	26.08
58.60	42.97	0.44	15.46	26.70
61.00	45.75	0.46	17.89	27.46
63.40	48.44	0.46	20.54	28.63
80.50	64.44	1.22	23.78	30.81
97.60	73.89	2.14	27.30	34.75
114.60	74.29	0.87	32.00	47.08
131.70	75.22	2.28	35.00	52.78
148.80	74.58	0.98	42.00	22.47
165.90	73.73	0.66	47.00	12.73
182.90	75.31	1.49	61.00	4.77
200.00	74.39	2.85	64.10	4.98