


ENERGIZER E95

D



Industry Standard Dimensions




Specifications

Classification:	Alkaline
Chemical System:	Zinc-Manganese Dioxide (Zn/MnO ₂) No added mercury or cadmium
Designation:	ANSI-13A, IEC-LR20
Nominal Voltage:	1.5 volts
Nominal IR:	150 to 300 milliohms (fresh)
Operating Temp:	-18°C to 55°C (0°F to 130°F)
Typical Weight:	144.0 grams (5.1 oz.)
Typical Volume:	56.0 cubic centimeters (3.4 cubic inch)
Jacket:	Plastic Label
Shelf Life:	10 years at 21°C
Terminal:	Flat Contact

Milliamp-Hours Capacity

Continuous discharge to 0.8 volts at 21°C



Device Selection Guide:

Battery Selection Indicator

Portable Stereo



Toy



Lighting



Radio



High Drain
Devices

Moderate Drain
Devices

Low Drain
Devices

Important Notice


This data sheet contains typical information specific to products manufactured at the time of its publication.
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

ENERGIZER E95

D


Constant Resistance Performance

Typical Characteristics (21°C)




Constant Current Performance

Typical Characteristics (21°C)




Industry Standard Tests (21°C)


RADIO 10 ohm 4 hrs/day




LIGHTING 1.5 ohm HIF



TOY 2.2 ohm 1 hr/day



PORTABLE STEREO 600 mA 2 hrs/day



Important Notice

This data sheet contains typical information specific to products manufactured at the time of its publication.
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.