

Resonators > CERALOCK (MHz) > Part Number

How to check EU RoHS Compliant of Our Products is [here](#).

Product Lifecycle Stage	in Production
Recommended Rank	Preferred

Specification

Global Part Number	CSTCC3M58G53A-R0
Previous Part Number	CSTCC3.58MGA-TC
Nominal Frequency	3.580MHz
Initial Tolerance	±0.5%
Temp. Stability	±0.4%
Temperature Range	-40 to +125°C
Wash	Available
Ultrasonic Wash	Available
Built-in Load Capacitance	15pF
Use	For automotive electronics

Minimum Quantity

180mm Paper Tape	
180mm Embossed Tape	2000
330mm Paper Tape	
330mm Embossed Tape	
Bulk Case	
Bulk(Bag)	
Ammo Pack	
320Reel	
Magazine	
Box	

Details

- ?  [Part Numbering](#)
- ?  [Appearance_1\(2.00_to_2.99MHz\)](#)
- ?  [Appearance/Dimensions_\(3.00MHz_-\)](#)
- ?  [Features_Applications](#)
- ?  [Temperature_Characteristics](#)
- ?  [Basic_Oscillation_Circuit](#)
- ?  [Standard_Land_Pattern_Dimensions](#)
- ?  [Notice_\(storage_and_operating_condition\)](#)
- ?  [Notice_\(rating\)](#)
- ?  [Notice\(Soldering_and_Mounting\)](#)
- ?  [Notice_\(handling\)](#)
- ?  [Packaging_2\(3.00MHz_-\)](#)
- ?  [Minimum_Quantity\[Supplementation\]](#)

Please approve our product specifications or to transact the approval sheet for product specifications before ordering. Please read rating and !Cautions first.
Product specifications in this catalog are as of January 2008.

All products and company names herein are trademarks or registered trademarks of their respective owners.