


PIN RECEPTACLES

FOR .040" - .050" DIAMETER PINS (#02 CONTACT)
FOR .040" - .060" DIAMETER PINS (#03 CONTACT)

0355

0355-0-15-XX-02-XX-10-0


Solder mount in .102 min. mounting hole



0354

0354-0-15-XX-02-XX-10-0


Pentagonal press-fit in .104 min. plated through-hole



3490

3490-0-15-XX-02-XX-10-0


Press-fit in .091 mounting hole



3808

3808-0-15-XX-02-XX-10-0


Press-fit in .090 mounting hole



9184

9184-0-15-XX-02-XX-40-0


Bottom entry, surface mount
 .092 min. plated through-hole
 Also available on carrier tape,
 See page 194.12 for Tape & Reel details



9222

9222-2-15-XX-02-XX-40-0


Bottom entry, surface mount
 .082 min. plated through-hole
 Also available on carrier tape,
 See page 194.12 for Tape & Reel details




4064

4064-0-18-XX-03-XX-40-0

Surface mount
 Also available on 16mm wide carrier tape:
 2,400 parts per 13" reel
 See page 194.13 for Tape & Reel details



P.C.B. Layout



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Inches

Tolerances On: Lengths: $\pm .005$

Diameters: $\pm .002$

Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - XX - XX - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

01 200 μ " TIN/LEAD OVER NICKEL

◆ **80** 200 μ " TIN OVER NICKEL (RoHS)

◆ **15** 10 μ " GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

01 200 μ " TIN/LEAD OVER NICKEL

◆ **80** 200 μ " TIN OVER NICKEL (RoHS)

◆ **27** 30 μ " GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#02 or #03 CONTACT (DATA ON PAGE 259)

(For alternate contact choices, see group F on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com