

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	ECR-16-013297	24JUL2017	FL	SY

D

D

C


C

B

B


A

A



NOTES:


- GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27µm NICKEL MIN.AND ACTION PIN: 0,5µm TIN MIN. FOR PLATING OF MATING SURFACES SEE PERFORMANCE LEVEL SHOWN IN PART NUMBER TABLE.
- MATERIAL; PHOSPHORBRONZE.
- ROW "f" 5 PLATED THROUGH HOLES FOR LOWERSHIELD.
- HOLE PATTERN FOR FEMALE CONNECTOR TYPE C WITH UPPERSHIELD, 55+6 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
- MAX. BOARD THICKNESS 3,5 mm.
- SHIELDS LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REF: TR-NWT-001217 ISSUE 1, SEPT. 1992.
- CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.
- CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 1.
- CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III,CENTRAL OFFICE APPLICATIONS.
- 0.76µm MIN GOLD PLATING AT MATING SURFACE.



COMPONENT SIDE AS SHOWN
RECOMMENDED PCB-HOLE LAY-OUT

P.C.B. HOLE DIM. ACTION PIN
FOR DETAILS SEE
APPLICATION SPECIFICATION

OBSOLETE	1 2 10	2	4-5352112-0
	1 6 9	2	5352112-9
	1 2	2	5352112-2
FINISH		MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.N.KIRAN 18AUG04		 TE Connectivity									
DIMENSIONS: mm		CHK B.MOOIJ 25MAR05											
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME Z-PACK 2mm HM GROUND RETURN LOWER SHIELD TYPE C/M									
		0-PLC ± -											
		1-PLC ± -											
		2-PLC ± -											
		3-PLC ± -											
		4-PLC ± -											
		ANGLES ± -											
MATERIAL -		FINISH -				SIZE A2		CAGE CODE 00779		DRAWING NO C=5352112		RESTRICTED TO -	
				WEIGHT 0.000000									
				CUSTOMER DRAWING				SCALE 5:1		SHEET 1 of 1		REV E	