

3M

Double Coated Tapes with Adhesive 350

9500PC • 9500B • 9593 • 3028EK

Technical Data

November, 2008

Product Description

3M™ Double Coated Tapes 9500PC, 9500B, 9593 and 3028EK feature a thin polyester film for dimensional stability and improved handling with ease of die-cutting and laminating. 3M™ Adhesive 350 is a medium-firm acrylic adhesive that provides a combination of high wet grab and initial adhesion and good shear holding power to a wide variety of materials, including many plastics.

Construction

Product Number	Faceside ¹ Adhesive Type/ Thickness	Carrier Type/ Thickness	Backside ² Adhesive Type/ Thickness	Liner Color, Type, Print	Liner Caliper	Total Tape Thickness (w/o liner)
3M tape 9500PC	350/ 0.0023" (0.058mm)	Clear PET ³ 0.001" (0.025mm)	350/ 0.0023" (0.058mm)	Natural, Polycoated Kraft, no print	0.0045" (0.11mm)	0.0056" (0.14mm)
3M tape 9500B	350/ 0.0023" (0.058mm)	Black PET ³ 0.001" (0.025mm)	350/ 0.0023" (0.058mm)	Natural, Polycoated Kraft, no print	0.0045" (0.11mm)	0.0056" (0.14mm)
3M tape 9593	350/ 0.0015" (0.038mm)	Clear PET ³ 0.0005" (0.013mm)	350/ 0.0015" (0.038mm)	White, 55#, Densified Kraft	0.0032" (0.081mm)	0.035" (0.089mm)
3M tape 3028EK	350/ 0.0023" (0.058mm)	Clear PET ³ 0.001" (0.025mm)	350/ 0.0023" (0.058mm)	White, Extensible Kraft, no print	0.0055" (0.14mm)	0.0056" (0.14mm)

Note 1: Faceside adhesive is on the interior of the roll, exposed when unwound.

Note 2: Backside adhesive is on the exterior of the roll, exposed when liner is removed.

Note 3: PET (Polyester).

The caliper listed is based on a calculation from manufacturing controlled adhesive coat weights using a density of 1.012 g/cc.

3M™ Double Coated Tapes with Adhesive 350

9500PC • 9500B • 9593 • 3028EK

Typical Physical Properties and Performance Characteristics	Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.		
	Product Number	3M™ Double Coated Tapes 9500PC, 9500B, 3028EK	3M™ Double Coated Tape 9593
Adhesion to stainless steel ASTM D3330 - 90 degree	- 15 minute RT	Oz/in (N/100mm) 71 (77)	Oz/in (N/100mm) 69 (75)
	- 72 hour RT	93 (101)	78 (85)
	- 72 hour 158°F (70°C)	121 (132)	72 (79)
ASTM D3330 - 180 degree, 2 mil al foil	- 72 hour RT	140 (153)	—
	ASTM D3330 - 180 degree, 2 mil polyester, stainless steel	—	91 (100)
Adhesion to other surfaces ASTM D3330 - 90 degree, 2 mil al foil, 72 hour RT	ABS	74 (81)	81 (89)
	Polycarbonate (PC)	60 (65)	77 (84)
	Polypropylene (PP)	44 (48)	—
	Polyester (PET)	77 (84)	—
	High Density Polyethylene (HDPE)	33 (36)	—
	Shear Strength - ASTM D3654 modified - (.5 inch ² sample size)		
	1000 grams at 72°F (22°C)	10,000 minutes	10,000 minutes
	500 grams at 158°F (70°C)	10,000 minutes	5,737 minutes
Relative High Temperature Operating Ranges:	Long Term (days, weeks)	200°F (93°C)	200°F (93°C)
	Short Term (minutes, hours)	350°F (177°C)	350°F (177°C)
Available Sizes	Roll length, width, slitting tolerance, core size.		
	Available Lengths, (Subject to Minimum order requirements)	3M Tapes 9500PC, 9500B, 9593 and 3028EK	
	Standard	36 yd (33 m)	
	Maximum Length		
	1/4" to 1/2"	144 yd (132 m)	
	1/2" to 48"	360 yd (329 m)	
	Available Widths		
	Minimum	1/4" (6.35 mm)	
	Maximum	48" (1220 mm)	
	Normal Slitting Tolerance	± 1/32" (0.8 mm)	
	Core Size	3.0" (76.2 mm)	

3M™ Double Coated Tapes with Adhesive 350

9500PC • 9500B • 9593 • 3028EK

Features

- 3M™ Adhesive 350 is a firm acrylic adhesive that provides very high adhesion to a wide variety of materials, excellent shear holding power, high temperature resistance and excellent UV resistance.
- 3M adhesive 350 provides exceptional temperature and chemical resistance and withstands tough application environment.
- 3M™ Double Coated Tape 9500PC has a moisture resistant liner which can withstand high humidity conditions with minimal cockling or wrinkling.
- These tapes have a film carrier, which can add dimensional stability to substrates. The carrier also provides easier handling during slitting and die-cutting.
- 3M™ Double Coated Tape 3028EK has an extensible kraft liner which facilitates narrow slitting.
- 3M™ Double Coated Tape 9593 clear polyester carrier provides dimensional stability and improved handling with ease of die cutting and lamination compared to adhesive transfer tapes.

Application Techniques

Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure helps develop better adhesive contact and improves bond strength.

To obtain optimum adhesion, the bonding surfaces must be clean, dry and well unified. Some typical surface cleaning solvents are isopropyl alcohol or heptane.*

Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

*Carefully read and follow the manufacturer's precautions and directions for use when working with solvents.

Application Ideas

- Dissimilar materials joining, such as metal to plastic.
- High performance joining and bonding.
- 3M tape 3028EK for applications which use narrow slit, level wound roll.

Application Equipment

To apply adhesives in a wide web format, lamination equipment is required to ensure acceptable quality. To learn more about working with pressure-sensitive adhesives please refer to technical bulletin, Lamination Techniques for Converters of Laminating Adhesives (70-0704-1430-8).

For additional dispenser information, contact your local 3M sales representative, or the toll free 3M sales assistance number at 1-800-362-3550.

3M™ Double Coated Tapes with Adhesive 350

9500PC • 9500B • 9593 • 3028EK

Storage	Store in original cartons at 70°F (21°C) and 50% relative humidity.
Shelf Life	If stored under proper conditions, product retains its performance and properties for two years from date of manufacture.
Certification/ Recognition	MSDS: 3M has not prepared a MSDS for these products which are not subject to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R. 1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, the products should not present a health and safety hazard. However, use or processing of the products in a manner not in accordance with the directions for use may affect their performance and present potential health and safety hazards. TSCA: These products are defined as articles under the Toxic Substances Control Act and therefore, are exempt from inventory listing requirements.
Technical Information	The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.
Warranty, Limited Remedy, and Disclaimer	Many factors beyond 3M's control and uniquely with user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.
Limitation of Liability	Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



Industrial Adhesives and Tapes Division Converter Markets

3M Center, Building 21-1W-10, 900 Bush Avenue
St. Paul, MN 55144-1000
800-223-7427 • 651-778-4244 (fax)
www.3M.com/converter



Recycled Paper
40% pre-consumer
10% post-consumer

3M is a trademark of 3M Company.
Printed in U.S.A.
©3M 2008 70-0709-3855-3 (11/08)