

2655 Napa Valley Corporate Dr., Napa, CA 94558

(707) 226-8600 FAX: (707) 226-9670

Date: May, 2004

Rev: 01

Connector, straight  
15A, 250V

Catalog Number: 320IEC15

- Item: Connector, appliance coupler.  
IEC 60320 standard sheet C15.
- Rating: For hot conditions (120°C rating).  
10 amperes, 250 volts ac: International.  
15 amperes, 250 volts ac (max): North America.
- Materials: Plastic parts are heat stabilized nylon with CTI greater than 400 volts.  
Contacts are solid brass.
- Contacts: One piece, .032" thick brass, double wipe.
- Terminals: Tempered brass, lug style, Perma-Lock™ design.
- Terminal Identification: Terminal screws are color coded.  
Wire entrance holes marked "L", "N" and "⊥".
- Cord Clamp: Internal. Accommodates 0.300" (18/3 SJ) through  
0.655" (12/3 S) North American cable,  
And 3 conductor .75 to 4.00 mm<sup>2</sup> harmonized cable.
- Overall Design: Two assembly screws, U-drive style.  
All screws are combination slot/cross head.  
Beveled housing. Dust seal at cord entry.  
Cable strip length gauge molded into connector body.
- Listings: UL listed, CSA certified.
- Dimensions:

