

No.200M Series Swivel Caster



Characteristic

No. 200M series is developed for medical use and it takes safety factor of 8 to have higher safeness and reliability.
Also, using a polybutadiene rubber made wheel for an excellent performance on cushion, it is a caster that makes little noise.

Application

Wheel chairs / Medical Instruments / Wagons, etc.

Specification

Model No.	F(Turning Radius)	Allowable Load(kg)	Net Weight(g)	Code No.
No.208M d=19	R110	50	820	9189
No.208M d=21				9190
No.208MSd=19			920	9197
No.208M d=21				9198
No.209M d=19	R125		900	9191
No.209M d=21				9192
No.209MSd=19			1010	9199
No.209MSd=21				9200
No.211M d=19	R174	45	1450	9195
No.211M d=21				9196
No.211MSd=19			1560	9203
No.211MSd=21				9204



Caster with stopper has S at the end of the model No.
Please specify the shaft diameter (d size). Available sizes are 19mm and 21mm.

Parts List

No.	Part Name	Material	Finish	Quantity
1	Main Body	SPCC	Uc	1
2	Main Axis	SWCH		1
3	Wheel	PBR	Black	1

Size List

Model No.	D	E	H	W	d
No.208M	φ130	45	163	22	19.21
No.209M	φ150	50	181		
No.211M	φ200	74	223	25	



with stopper

