




SIGN	DATE	DESCRIPTION	APPROVER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

- Material:
- Insulator(housing): Thermoplastic (UL94V-0)
 - Insulator(cover): Thermoplastic (UL94V-0)
 - Metal housing: Steel
 - Terminal screw: Steel Zinc plating "-" slot type.
 - Contact: Brass,Tin plated.

- Electrical:
- cULus
- Voltage rating: 300V
 - Current rating: 8A
 - Wire range:
 - Solid wire(AWG): 16-28
 - Stranded wire(AWG): 16-28
 - Torque: 1.7 Lb-In.
 - Screw: M2
 - Wire strip length: 8-9mm
 - Withstanding Voltage: 1.6KV
 - Operating temperature: -40°C to +115°C

RoHS Compliant

PART NUMBER:

OSTTRXX3550

No. of Poles
02 2 Poles
03 3 Poles
...
24 24 Poles

COLOR
0: Black
5: Green (Standard)
6: Blue
8: Grey



TITLE		OSTTR 3.81mm 90D Series										
PART NO.		OSTTRXX3550					DWG NO.		OSTTRXX3550.DWG			
APPROVED		CHECKED	DESIGNED	DRAWN		CUST NO.		Tolerance				
				Tony					UNIT: mm	X.	±0.50	
				Tony					SCALE: NONE	X.X	±0.30	
				2008.06.10				SHEET: 01/01		REV.: B	X.XX	±0.10
											X°	±1°