



PART NUMBER	ITEM ① SHROUD BODY	ITEM ② INSULATOR	ITEM ③ PIN
127-0711-601	KOVAR GOLD PL .00005 MIN OVER NICKEL PL	GLASS, CORNING 7070 OR EQUIVALENT	KOVAR GOLD PL .00005 MIN OVER NICKEL PL



DRAWING NO. B-127-0711-601/610									
0		REVISIONS							
ENGINEERING RELEASE									
1	1-4-07	P A T	J R K	J C N				1-18-07	ECN 50860

CUSTOMER DRAWING

THIS DRAWING TO BE INTERPRETED
PER ASME Y 14.5M - 1994

"μSTATION"

COMPANY CONFIDENTIAL

NOTES:

1. SPECIFICATIONS:

ELECRICAL:

IMPEDANCE: 50 OHMS NOMINAL
FREQUENCY RANGE: DC TO 18 GHZ
VSWR: DEPENDANT ON APPLICATION

ENVIRONMENTAL:

HERMETICITY: 1×10^{-8} cc/sec AT ONE ATMOSPHERE
SOLDERABILITY: MEETS REQUIREMENTS OF MIL-STD-202G, TEST METHOD 208H.
OPERATING TEMPERATURE: -55 DEG C TO +165 DEG C

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY PAT	DATE 11-21-06	 Connectivity Solutions P.O. Box 1732 Waseca, MN 56093 1-800-247-8256	
DECIMALS	mm				
.XX		CHECKED BY JRK	DATE 1-18-07	TITLE SMP FULL DETENT STRAIGHT FEEDTHRU SHROUD HERMETIC SEALED PIN CONTACT	
.XXX ±.003					
MATL		APPROVED BY JCN	DATE 1-18-07	SHEET 2 OF 2	
FINISH					
		RELEASE DATE 1-18-07		DRAWING NO. B - 127-0711-601/610	
		U/M	INCH	SCALE	15:1