

TIGER™
EYE
SYSTEM



MH-130-02-L-D-LC




HIGH-RELIABLE HORIZONTAL

RV[®]
FILE NO. E111594

**TIGER™
EYE**

Technical drawing of a mechanical part with dimensions and tolerances:

- Top dimension: $(0.64) \text{ .025 TYP}$ with a tolerance arrow pointing to the right.
- Left side dimensions: $(4.57) \text{ .180}$ with a tolerance arrow pointing to the left.
- Right side dimensions: $(1.65) \text{ .065}$ with a tolerance arrow pointing to the right, and $(2.03) \text{ .080}$ with a tolerance arrow pointing to the left.



Technical drawings of the 1000 Series 1/2. The left drawing is a side view showing a series of rectangular features with a dimension of $(0.41) .016$ and a tolerance of $\pm .005$. The right drawing is a cross-sectional view showing a central cavity with a dimension of $(1.50) .059$ and a tolerance of $\pm .005$. The label **-WT** is positioned below the drawings.

-FR
= Full Reel Tape & Reel
(must order max. quantity
per reel; contact Samtec
for quantity breaks)

HORIZONTAL

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.