

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION





.19

(C) COPYRIGHT 19


BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
CM	53	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E	REV & REDWN PER EC 0G1B-0217-98	29OCT98	TB	R5


1. WIRE RANGE: 2 - 6 mm² (14 - 10 AWG)
2. INSULATION RANGE: 2.54 - 4.57
- △3 FRICTION FIT ON A 3.56 DIAMETER PIN.




SECTION A-A



SECTION C-C



SECTION B-B



SECTION D-D

2.03	.080	4.32	.170	5.48	.216	-	-
1.52	.060	4.06	.160	5.46	.215	-	-
0.36	.014	3.94	.155	5.08	.200	-	-
0.35	.014	3.56	.140	4.57	.180	20.19	.795
0.13	.005	2.54	.100	4.45	.175	6.05	.238
MM	IN	MM	IN	MM	IN	MM	IN

CONVERSION TABLE

METRIC

PRE TIN	0.36 PH BRZ	350200-2
PRE TIN	0.35 BRASS	350200-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. BECK 29OCT1998	AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK R. SWING 29OCT1998	NAME C. MARTIN	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.13 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH SEE TABLE		APVD C. MARTIN 16NOV1998	PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING	
MATERIAL SEE TABLE		SIZE A2	CAGE CODE 00779	DRAWING NO C- 350200
		SCALE 5:1	SHEET 1 OF 1	REV E