


LOC	DIST	REVISIONS						
GP	00	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
				B		REVISED & REDRAWN PER ECN-2262	-	-
				C		REVISED ECN-2364	8-1-88	L5 RW
				D		RLSE 1-1 PER NPR 3095, WAS 90-5898-17	09/04/90	-
				E		RLSE 1-3 PER NPR 3342, WAS 91-5898-1-2	2-13-91	BT
				F		REVISED PER ECN BD5212	06/26/91	-
				G		ADDED 1-6 PER NPR 3626, WAS 91-5898-18	07/12/91	-
				H		OBS -11 PER EC OUID-0251-00	23 JAN 01	DK
				J		REV PER EC OUE0-0002-01	09 JAN 02	JR



1	.042	.415	1-206943-6
2	.041	.305	1-206943-3
2	.056	.290	1-206943-1
1	.030	.450	206943-7
1	.030	.290	206943-5
3	.030	.415	206943-3
1	.030	.415	206943-2

- 1 ZINC PLATED PER ASTM B633, TYPE II, CLASS SC1, YELLOW CHROMATE.
- 2 ZINC PLATED PER ASTM B633, TYPE II, CLASS SC1, CLEAR CHROMATE.
- 3 OBSOLETE.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± .005 3 PLC DEC ± .005 ANGLES ± -		DR 6-6-BB C. RICHARD CHK 6-15-BB W. LENKER APPD 6-16-BB B. WYNN APPD 6-17-BB V. KUMAR	AMP INCORPORATED Harrisburg, Pa. 17105	
MATERIAL COLD ROLLED STEEL PER ASTM A108		PRODUCT SPEC -	NAME SLIDELATCH SCREW, #4-40, AMPLIMITE TM	
FINISH SEE TABLE		APPLICATION SPEC -	SIZE B	FSCN NO 00779
		WEIGHT -	SCALE 10:1	DRAWING NO 206943
			SHEET 1 OF 1	