

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

171814-0002

Status:

Active

Overview:

KK® Interconnect System

Description:

KK® 396 RPC Wire-to-Board Right-Angle Header with Friction Lock, 2 Circuits

Documents:

3D Model

Product Specification PS-171813-0002 (PDF)

Drawing (PDF)

Test Summary TS-171813-0001 (PDF)

Product Specification PS-171813-0001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

PCB Headers

Series

171814

Application

Power, Signal, Wire-to-Board

Overview

KK® Interconnect System

Product Name

KK® 396

UPC

887191375649

Physical

Breakaway

No

Circuits (Loaded)

2

Circuits (maximum)

2

Color - Resin

Black

Durability (mating cycles max)

25

First Mate / Last Break

No

Flammability

94HB

Glow-Wire Compliant

Yes

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Plating Mating

Tin

Material - Plating Termination

Nickel

Material - Resin

Nylon

Net Weight

0.780/g

Number of Rows

1

Orientation

Right Angle

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Pitch - Mating Interface

3.96mm

Shrouded

Partial

Stackable

No

Surface Mount Compatible (SMC)

No

Temperature Range - Operating

-40°C to +105°C

Termination Interface: Style

Through Hole

Electrical

Current - Maximum per Contact

7A

Voltage - Maximum

250V

Solder Process Data

Duration at Max. Process Temperature (seconds)

30

Lead-free Process Capability

SMC & Wave Capable (TH only)



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

171814Series

Max. Cycles at Max. Process Temperature	3
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Product Specification	PS-171813-0001, PS-171813-0002
Sales Drawing	SD-171814-0001
Test Summary	TS-171813-0001

This document was generated on 10/07/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION