

Type CDLC Axial 3000 F, Ultracapacitors

Large Cylindrical Type 3000 F



This leading edge large cell ultracapacitor, with low RC time constants, offers flexible mounting with two M6 thread holes on each end in weldable terminals. They are especially suited for backup and pulse power applications such as grid stabilization and wind turbine pitch control. When assembled into modules, the low connection resistance design excels in transportation applications like automotive subsystems, rail system power and utility vehicles.

Highlights

- Maximum Power Performance at 3000 Farads
- Very Low ESR
- Low Thermal Resistance (4 °C/W)

Specifications

Operating Temperature Range	-40 °C to +65 °C
Storage Temperature Range	-40 °C to +70 °C
Rated Voltage Range	2.7 Vdc, 2.85 Vdc rated surge
Capacitance Range	3000 F
Capacitance Tolerance	0% / +10%
Life at Room Temperature	10 years at rated voltage and 25 °C Capacitance change ≤20% ESR change ≤100%
Life Test	1000 h @ rated voltage and +65 °C Capacitance change ≤20% decrease from initial specified value ESR change ≤100% increase from initial specified value
Cycle Test	>1,000,000 cycles (rated to half rated voltage at +25 °C) Capacitance change ≤20% ESR change ≤100%
Shelf Life	1000 h without voltage at +70 °C Capacitance change ≤20% from min. initial capacitance ESR change ≤100% from max. initial ESR
RoHS Compliant	

Ratings


Part Number	CDLC302P2R7LR
Terminal Configuration	Axial M6 Threaded Tap
Capacitance (F) (Discharge w constant current at 25 °C)	3000
ESR, DC (mΩ), Max	0.26
Current - Max Peak (A) (1 s discharge rate to 50% of rated Voltage)	2300
Leakage current (mA), Max after 72 h at +25 °C	5
Usable Power Density, Pd (W/kg) (Per IEC 62391-2)	6600
Usable Power (W)	3365
Impedance match power, (W/kg)	16200
Gravimetric energy density, Emax (Wh/kg)	6.0
Energy available (Wh) (At rated voltage)	3.04
Weight (kg)	0.51
Maximum Continuous Current (Arms) (for +20 °C temperature rise)	145
Short circuit current (A)	10,000

Type CDLC Axial 3000 F, Ultracapacitors

Part Numbering System

CDLC Type	302 Capacitance (F)	P Tolerance (%)	2R7 Voltage (V)	LR Configuration
CDLC - Carbon Double Layer Cell	302 = 3000	P = 0 /+10%	2R7 = 2.7	LR = axial M6 thread tap

Outline Drawing and Dimensions



Do not reverse polarity.

Notice and Disclaimer: All product drawings, descriptions, specifications, statements, information and data (collectively, the "Information") in this datasheet or other publication are subject to change. The customer is responsible for checking, confirming and verifying the extent to which the Information contained in this datasheet or other publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without any guarantee, warranty, representation or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on the knowledge that the Cornell Dubilier company providing such statements ("Cornell Dubilier") has of operating conditions that such Cornell Dubilier company regards as typical for such applications, but are not intended to constitute any guarantee, warranty or representation regarding any such matter – and Cornell Dubilier specifically and expressly disclaims any guarantee, warranty or representation concerning the suitability for a specific customer application, use, storage, transportation, or operating environment. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by Cornell Dubilier with reference to the use of any Cornell Dubilier products is given gratis (unless otherwise specified by Cornell Dubilier), and Cornell Dubilier assumes no obligation or liability for the advice given or results obtained. Although Cornell Dubilier strives to apply the most stringent quality and safety standards regarding the design and manufacturing of its products, in light of the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies or other appropriate protective measures) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage. Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated in such warnings, cautions and notes, or that other safety measures may not be required.

OBSOLETE