



NO	DESCRIPTION	DATE
①	CHANGE THE DIRECTION OF BAYONET	03.03.97'
②	$31.7 \pm 0.4 \rightarrow 31.5 \pm 0.3$	03.14.02'
③	BACKGROUND FORMAT UPDATED	02.23.04'
④	BACKGROUND FORMAT UPDATED $17.0 \rightarrow 16.5$	04.30.09'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-1 GHz
1.2 NOMINAL IMPEDANCE: 75 OHM
1.3 WORKING VOLTAGE: 500 VOLTS MAX.
1.4 PROOF VOLTAGE: 1500 VOLTS

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
2.2 CENTER CONTACT: BERYLLIUM COPPER PER ASTM B196 UNS C17300
2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
2.4 CRIMP FERRULE: BRASS PER JIS-C2700

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.



4.0 MECHANICAL

- 4.1 FOR USE WITH RG59U OR SIMILAR STYLE CABLE
4.2 CABLE ATTACHMENT: OUTER: CRIMP, INNER: SOLDER/CRIMP
4.3 CRIMP SIZE REQUIRED: CONTACT: 1.8(.071) HEX. CRIMP TOOL
FERRULE: 6.5(.256) HEX. CRIMP TOOL

5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -65° C TO +165° C

5	CHASSIS	BRASS	1	SILVER 70 μ " MIN.
4	BODY	BRASS	1	SILVER 70 μ " MIN.
3	INSULATION	TEFLON	1	NONE
2	CENTER CONTACT	BERYLLIUM COPPER	1	SILVER 70 μ " MIN.
1	CRIMP FERRULE	BRASS	1	SILVER 70 μ " MIN.
<i>NO</i>	<i>DESCRIPTION</i>	<i>MATERIAL</i>	<i>Q' TY</i>	<i>FINISH</i>



STRIPPING DIMENSION

FARNELL ORDER CODE: 1169591

DESCRIPTION			BNC STRAIGHT JACK CRIMP									
製圖	DRAWN	TOLERANCE		品名	13-15-1 T.S.S 59U			日期	DATE	版次	REV.	
	Yoko			\ROHS COMPLIANT (75U)			07.03.96		A-4			
檢圖	CHECK	,XX	±0.1	單位	UNIT	DWG.NO. 13-0365						
	Arc				mm(in)							
認定	APPROVAL	,XXX	±0.05	比例	SCALE	 佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.						
	Lewis				ANGLE							±5°