

**Broadband Solutions**

CX3499969 | 150T110PP200ROPE COEX

**ConQuest® Empty Conduit, 1 1/2 in, SDR 11, terracotta, with pull rope**

## Dimensions

|                            |                       |
|----------------------------|-----------------------|
| Nominal Size               | 1-1/2 in              |
| Wall Thickness Designation | SDR 11                |
| Inner Diameter, nominal    | 38.964 mm   1.534 in  |
| Length                     | 914.40 m   3000.00 ft |
| Outer Diameter, nominal    | 48.260 mm   1.900 in  |
| Wall Thickness, minimum    | 4.394 mm   0.173 in   |
| Weight                     | 416.0 lb/kft          |

## General Specifications

|              |              |
|--------------|--------------|
| Color        | Terracotta   |
| Conduit Type | Non-toneable |
| Wall Type    | Smooth       |
| Brand        | ConQuest®    |
| Warranty     | One year     |

## Material Specifications

|                                       |                                     |
|---------------------------------------|-------------------------------------|
| Density Test Method                   | ASTM D792A                          |
| Density, maximum                      | 0.955 g/cm <sup>3</sup>             |
| Density, minimum                      | 0.941 g/cm <sup>3</sup>             |
| Design Standard                       | ASTM D3350-05                       |
| Environmental Stress Crack Resistance | Failure rate of 10% within 96 hours |
| Environmental Stress Test Method      | ASTM D1693, ESCR Condition B        |
| Flexural Modulus, minimum             | 552 N/mm <sup>2</sup>   80000 psi   |
| Flexural Property Test Method         | ASTM D790                           |
| Hydrostatic Design Basis              | Not pressure rated                  |
| Hydrostatic Design Test Method        | ASTM D2837                          |
| Material Type                         | High density polyethylene (HDPE)    |
| Melt Flow Rate Test Method            | ASTM D1238                          |
| Melt Flow Rate, maximum               | 0.39 g/10 min                       |
| Tensile Property Test Method          | ASTM D638                           |
| Tensile Strength at yield, minimum    | 21 N/mm <sup>2</sup>   3000 psi     |

## Mechanical Specifications

|                                  |                    |
|----------------------------------|--------------------|
| Minimum Bend Radius, unsupported | 508.0 mm   20.0 in |
|----------------------------------|--------------------|

CX3499969 | 150T110PP200ROPE COEX

Pulling Tension, maximum 798.3 kg | 1760.0 lb

## Pull Line Specifications

|                   |                    |
|-------------------|--------------------|
| Breaking Strength | 90.7 kg   200.0 lb |
| Material Type     | Polypropylene      |
| Pull Line Type    | Rope               |

## Regulatory Compliance/Certifications

| Agency        | Classification                                                                 |
|---------------|--------------------------------------------------------------------------------|
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |

## \* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance