



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS			DOC. NO. SPC-F005 * Effective: 12/21/98 * DCP No. B80					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
B44	A	Released	JWM	01/04/02	HYO	1/24/02	DJC	1/24/02



Specifications

1. Current Rating: 1 AMP
2. Voltage Rating: 250 VRMS
3. Dielectric Withstanding Voltage: 500 VRMS Min.
4. Insulation Resistance: >5000 Megohms
5. Contact Resistance: 10 milliohms (Typ)
30 milliohms (Max)
6. Temperature Range: -65°C to +125°C
7. Insulation Material: Black, UL94V-0
Glass filled polyester
8. Contact Material: Phosphor Bronze
9. Contact Plating: 250 μ" Tin

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

UNLESS OTHERWISE SPECIFIED,

DRAWN BY: Jeff McVicker
CHECKED BY: Hiam Odish
APPROVED BY: Daniel Carey

DATE: 01/04/02
DATE: 1/24/02
DATE: 1/24/02

DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

SIZE: A

DWG. NO. SP-16-2T

ELECTRONIC FILE 31N2923.dwg
REV A