


Side View Surface Mount LEDs

SEC4001 Series

Part Number	Emitting Color	Lens Color	Forward Voltage		Conditions IF (mA)	Luminous Intensity		Conditions IF (mA)	Peak Wavelength		Conditions IF (mA)	Dominant Wavelength		Conditions IF (mA)	Spectrum Half Bandwidth		Chip Material
			VF (V) TYP	MAX		Iv (mcd) TYP	Conditions IF (mA)		λ_P (nm) TYP	Conditions IF (mA)		λ_d (nm) TYP	Conditions IF (mA)		$\Delta\lambda$ (nm) TYP	Conditions IF (mA)	
SEC4201C	Red	Water clear	1.9	2.5	10	10	20	630	10	620	10	35	10	35	10	10	GaAsP
* SEC4801C	Amber	Water clear	1.9	2.5	10	16	20	610	10	605	10	35	10	35	10	10	GaAsP
SEC4901C	Orange	Water clear	1.9	2.5	10	13	20	587	10	590	10	33	10	33	10	10	GaAsP
* SEC4701C	Yellow	Water clear	2.0	2.5	10	25	20	570	10	571	10	30	10	30	10	10	GaP
* SEC4401C	Green	Water clear	2.0	2.5	10	22	20	560	10	567	10	20	10	20	10	10	GaP
* SEC4401E-TG	Deep green	Transparent green	2.0	2.5	10	11	20	558	10	564	10	20	10	20	10	10	GaP
SEC4501C	Pure green	Water clear	2.0	2.5	10	8.0	20	555	10	559	10	20	10	20	10	10	GaP
SECU4401C-TG	High luminosity	Green	2.1	2.5	20	25	20	564	20	564	20	12	20	12	20	20	AlGaInP
* SECT4D01C-S	Ultrahigh	Pure green	3.3	4.0	20	150	20	525	20	520	20	35	20	35	20	20	InGaP
* SECT4E01C-S	luminosity	Blue	3.3	4.0	20	50	20	468	20	465	20	25	20	25	20	20	InGaP


*Mass production in preparation

Directional Characteristics (representative example)



External Dimensions

(Unit: mm)



5-1 Visible Light LEDs

Absolute Maximum Ratings

●Visible Light Unicolor Lamp

Parameter	Unit	Ratings					Conditions
		GaP	GaAsP	GaAlAs	AlGaInP	InGaN	
P _D	mW	75				120	
I _F	mA	30					
ΔI _F	mA/°C	-0.45					25°C or higher
I _{FP}	mA	100				70	f=1kHz, tw≤100μs
V _R	V	3			5		
T _{op}	°C	-30 to +85				-30 to +80	
T _{stg}	°C	-30 to +100					

●Visible Light Bicolor Lamp

Parameter	Unit	Ratings					Conditions
		GaP	GaAsP	GaAlAs	AlGaInP	InGaN	
P _D	mW	75				120	Same conditions for simultaneous lighting
I _F	mA	30					
ΔI _F	mA/°C	-0.45					25°C or higher
I _{FP}	mA	100					f=1kHz, tw≤100μs
V _R	V	4			5		
T _{op}	°C	-30 to +85					
T _{stg}	°C	-30 to +100					

●Visible Light Unicolor Surface Mount LEDs

Parameter	Unit	Ratings					Conditions
		GaP	GaAsP	GaAlAs	AlGaInP	InGaN	
I _F	mA	30				20	
ΔI _F	mA/°C	-0.45				-0.27	25°C or higher
I _{FP}	mA	100 ^{*1}				70 ^{*2}	f=1kHz, tw≤100μs
V _R	V	3			5		
T _{op}	°C	-30 to +85				-30 to +80	
T _{stg}	°C	-30 to +100					

*1: 70mA for SEC1005/1007 Series

*2: 50mA for SEC1005/1007 Series

●Visible Light Bicolor Surface Mount LEDs

Parameter	Unit	Ratings	Conditions
		SEC2002/2004	
Pd	mW	75	
		(Same conditions for simultaneous lighting)	
If	mA	30	
ΔIf	mA/°C	−0.45	25°C or higher
IfP	mA	70	f=1kHz, tw≤100μs
VR	V	4	
Top	°C	−30 to +85	
Tstg	°C	−30 to +100	

●Visible Light Three Element Surface Mount LEDs

Parameter	Unit	Ratings		Conditions
		SECT3M02C-S		
		Red	Green/Blue	
P _D	mW	75	120	When one chip lights up (same as green/blue for simultaneous lighting)
I _F	mA	30		
ΔI _F	mA/°C	−0.45		25°C or higher
I _{FP}	mA	70	50	f=1kHz, t _w ≤100μs
V _R	V	5		
T _{op}	°C	−30 to +80		
T _{sta}	°C	−30 to +100		