



I 2 3 4

A





B

B

C

C



Copyright FCI.

D

D

CONFIDENTIAL

rev	ecn no	dr	date
A	S90203	BSL	1999-11-02
B	S00048	JPEH	2000-03-28
C	S05-0103	KBM	2005-04-08
D	S10-0207	AK	2010-03-04
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface - ☒ ISO 1302	tolerance std ISO 406 ISO 1101	projection ☒ ☐	MM/INCH
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	JPEH	2000-03-28	ANGULAR	LINEAR	X.X/.XX	±0.3/.01
Eng	JPEH	2000-03-28			X.XX/.XXX	±0.13/.005
Chr	KH LEE	2010-03-04	0° ±2°		X.XXX/.XXXX	±0.051/.0020
Appr	JOEY NG	2010-03-04	Product family			LPVCC
			Spec ref			-
			LPVCC SMT 2.3 BOTTOM ENRTY ASSY, STACKABLE, WITH 0.64/.025 LOCATING FEATURES			Rev. D
			catalog no			-
			CUSTOMER			sheet 1 of 2

REV E - 2006-03-28

I 2 3 4

PDM: Rev:D STATUS Released Printed: Oct 14, 2010



Copyright FCI.




10. A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

NOTES:

1. HOUSING MATERIAL : HIGH TEMP PLASTIC.
2. TERMINAL MATERIAL: BeCu.
3. TERMINAL RETENTION 0.5Kg/1.1 Lbs.
4. PRODUCT DESCRIPTION CODE:
XXXXX-XXXLF
LEAD FREE (SEE NOTES 7 & 9)
TOTAL POSITIONS
CONTACT AREA PLATING
BASE NUMBER
5. PACKAGING:
(a) XXXXX-XXX --- STD PACKAGING IN TUBE.
(b) XXXXX-XXXTR --- TAPE AND REEL (CONDUCTIVE) PACKAGING WITH PICK-UP CAP (SEE FIG 1).
(c) XXXXX-XXXTRN --- TAPE AND REEL (CONDUCTIVE) PACKAGING WITHOUT PICK-UP CAP.
6. "V" CUT OPTIONAL - MANUFACTURING PROCESS OPTION.
7. SOLDERTAIL PLATING:
a) SOLDERTAIL OF P/N: 63467 - XXX IS TIN/LEAD PLATED.
b) SOLDERTAIL OF P/N: 63467 - XXXLF IS 100% MATTE TIN PLATED.
8. THE HOUSING WILL WITHSTAND EXPOSURE TO 255° C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
9. THIS PORODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

PRODUCT NO SEE NOTE 4	POSITIONS	DIM. A	DIM. B	DIM. C
63467-X10	2 X 5	8.00/.315	9.74/.383	6.00/.236
-X20	2 X 10	18.00/.709	19.74/.777	16.00/.630
-X30	2 X 15	28.00/1.102	29.74/1.171	26.00/1.024

CONTACT AREA PLATING OPTIONS	
1 = 0.76µm/30µ" Au	CONTACT AREA
3 = 0.38µm/15µ" Au	CONTACT AREA



RECOMMENDED PAD LAYOUT





FIG. 1
SEE NOTE 5(b)

CONFIDENTIAL

www.fciconnect.com			surface ISO 1302		- ✓ tolerance std ISO 406 ISO 1101		projection 		MM / INCH 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	JPEH	2000-03-28	ANGULAR	LINEAR	X.X/.XX		±0.3/.01		size A3	Scale 10:1	
Eng	JPEH	2000-03-28			X.XX/.XXX		±0.13/.005				
Chr	KH LEE	2010-03-04	0°		±2°	X.XXX/.XXXX		±0.051/.0020			
Appr		JOEY NG	2010-03-04		Product family LPVCC				Spec ref -		
		title LPVCC SMT 2.3 BOTTOM ENRTY ASSY, STACKABLE, WITH 0.64/.025 LOCATING FEATURES				dwg no 63467				Rev. D	
		catalog no -				CUSTOMER				sheet 2 of 2	