



FEATURES:

- Pincer patch cord interfaces directly into the most popular multimeters configured with non-sheathed style banana jacks, including Amprobe, Fluke, H-P, Tektronix and Wavetek.
- Plug is molded directly to the cable in an integral one-piece design for a long lasting connection.
- Attaches to component leads up to .090" (2.3 mm)
- Banana plug features top and side stacking for added test versatility.
- High strand count silicone insulated wire offers excellent flexibility and high temperature resistance.

MATERIALS:

Pincer: Body: Nylon – Fire Retardant – UL94 V-0 Rated, Color per part number

Pincer Contacts: Beryllium Copper, Gold Plated

Wire: 18 AWG, 65 x 36 t.c., Insulation – Silicone, .144" (3.66 mm) O.D., Color per P/N.

Banana Plug: Body - Brass, Nickel Plated, Spring – Beryllium Copper, Nickel Plated

Insulation: Polypropylene, Color per part number

RATINGS:

IEC 1010 2-031

Operating Voltage: Handheld Testing: 30 VAC / 60 VDC Max.

Hands Free Testing in Controlled Voltage environments: 300 VRMS Max.

Current: 5 Amperes

ORDERING INFORMATION: Model 6298-XX-*

XX = Lead Length in Inches, Standard Lengths: 12" (30.48 cm), 24" (61 cm), 36" (91.4 cm)

*= Color Code, -0 Black and -2 Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[6298-12-0](#) [6298-12-2](#) [6298-36-2](#) [6298-36-0](#) [6298-24-0](#) [6298-24-2](#)