

Housing - HC-B 24-SFQD-67/O1PG21 - 1674118

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid
(<http://download.phoenixcontact.com>)



Box mounting base, for double locking latch, height 67 mm, without screw connection, 1x Pg21, with protective covers



Key commercial data

Packing unit	1 PCE
Weight per Piece (excluding packing)	436.61 GRM
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	67 mm
Width	57 mm
Length	144 mm

Ambient conditions

Degree of protection of housing (IP)	IP65 (When plugged in)
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-B24, BB46, D64, DD108, M
Design	B24
Housing type	Box mounting bases
Locking type	For double locking latch
No. of cable exits	1
Cable exit	Left (view of the opened protective cover)
Screw connection	None
Type of the screw connection	1x Pg21

Housing - HC-B 24-SFQD-67/O1PG21 - 1674118

Technical data

General

Protective cover	Yes
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR
Material, protective cover	Polyamide

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

GOST

Housing - HC-B 24-SFQD-67/O1PG21 - 1674118

Approvals

Ex Approvals

Approvals submitted

Approval details

GOST 

Drawings

Dimensioned drawing

