


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS			DOC. NO. SPC-F005 * Effective: 12/21/98 * DCP No. 860					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
830	B	Updated Redrawn	JWM	3/16/02	JC	3/16/01	JC	3/16/01
1319	C	Dimensions Added	HQ	2/14/02	JC	2/14/02	JC	2/14/02



**NOTES:**

1. Material & Plating  
Body: Brass - Nickel Plated  
Nut: Brass - Nickel Plated  
Pin: Brass - Tin Plated  
Contact Pin: Phosphor Bronze - Tin 2.  
Plated
- Dielectric: PE
3. Working Voltage: DC 50V or AC 30V
4. Voltage Standing: DC 500V
5. Insertion Loss: 5 ~ 1000MHz <-0.5dB

DISCLAIMER  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

**SPC TECHNOLOGY**

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.		DRAWING TITLE: "F" Female to "F" Male Voltage Blocking Coupler	
DRAWN BY:	DATE:	SIZE	DWG. NO.
Jeff McVicker	8/17/98	A	1592
CHECKED BY:	DATE:	ELECTRONIC FILE	REV
JOHN COLE	8/18/98	92N3416.dwg	C
APPROVED BY:	DATE:	SCALE:	SHEET:
Daniel Carey	8/18/98	NTS	1 OF 1