




(2.54 mm) .100"

SLW, CES SERIES

LOW-PROFILE SOCKET STRIPS

SLW Mates with:

TLW, TSW, MTLW, MTSW,
HW, EW, ZW, HTSW,
HMTSW, TSM

CES Mates with:

TLW, TSW, MTLW,
MTSW, HW, EW, ZW,
DW, HTSW, PHT, HMTSW

SPECIFICATIONS

For complete specifications
see www.samtec.com?SLW
or www.samtec.com?CES

Insulator Material:

Black G.F. Polyester

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over

50 μ " (1.27 μ m) Ni

SLW Current Rating

(SLW/TSW):

5.2 A per pin

(2 pins powered)

CES Current Rating

(TSW/CES):

5.5 A per pin

(2 pins powered)

Voltage Rating:

SLW: 406 VAC

CES: 400 VAC

Operating Temp Range:

-55 °C to +125 °C with Gold

-55 °C to +105 °C with Tin

Insertion Depth:

SLW: (2.16 mm) .085" to

(2.92 mm) .115"

CES: (2.62 mm) .103" to

(4.06 mm) .160"

RoHS Compliant:

Yes

Lead-Free Solderable:

No, Lead Wave only

RECOGNITIONS

For complete scope
of recognitions see
www.samtec.com/quality





ALSO AVAILABLE (MOQ Required)

- Other platings

Note:

Some lengths, styles and
options are non-standard,
non-returnable.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.