




- 1 0.38µm [.000015] MIN GOLD ON MATING AREA,
1.27µm [.000050] MIN BRIGHT TIN-LEAD ON CRIMP AREA, BOTH OVER
1.27µm [.000050] MIN NICKEL.
- 2 2.54µm [.000100] MIN BRIGHT TIN-LEAD, OVER
1.27µm [.000050] MIN NICKEL.
- 3 GOLD FLASH ON CRIMP AREA,
2.54µm [.000100] MIN TIN ON MATING AREA, BOTH OVER
1.27µm [.000050] MIN NICKEL.
- 4 0.38µm [.000015] MIN GOLD ON MATING AREA,
GOLD FLASH ON CRIMP AREA, BOTH OVER
1.27µm [.000050] MIN NICKEL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 6 GOLD PLATING MAY OR MAY NOT BE PRESENT ON THE BOTTOM OF THE CRIMP BARREL

5 OBSOLETE	4	487923-5
3	6	487923-4
5 OBSOLETE	1	487923-3
	2	487923-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.OBERMAN 3-7-90	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK R.STONE 3-8-90				
		APVD -	NAME			
		PRODUCT SPEC -	CONTACT, SOLDER TAB, .050 C/L			
MATERIAL PHOSPHOR BRONZE		APPLICATION SPEC -	SIZE A2		CAGE CODE 00779	
		FINISH SEE TABLE	DRAWING NO C=487923		RESTRICTED TO -	
CUSTOMER DRAWING			SCALE 10:1	SHEET 1 OF 1	REV D1	