

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

Tyco Electronics AMP GmbH

ALL RIGHTS RESERVED.

LOC

DIST

FT

0

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD



CI

REVISED PER ECO-12-007964

02MAY2012

KH

MS



282965-3 AS SHOWN



MATERIALS AND FINISH  
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.  
TERMINAL: COPPER ALLOY, TIN PLATED.



2 SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.

3 RECOGNIZED UNDER THE COMPONENT PROGRAM OF  
UNDERWRITERS LABORATORIES INC., FILE N° E60677.

4 IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY  
WITH IEC 998-1/998-2-1.




NOT CUMULATIVE TOLERANCE.



|       |    |            |
|-------|----|------------|
| 89.64 | 12 | 1-282965-2 |
| 82.02 | 11 | 1-282965-1 |
| 74.40 | 10 | 1-282965-0 |
| 66.78 | 9  | 282965-9   |
| 59.16 | 8  | 282965-8   |
| 51.54 | 7  | 282965-7   |
| 43.92 | 6  | 282965-6   |
| 36.30 | 5  | 282965-5   |
| 28.68 | 4  | 282965-4   |
| 21.06 | 3  | 282965-3   |
| 13.44 | 2  | 282965-2   |

DIM. A N° OF POS. PART NUMBER

RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN E. ZANOLINI 09OCT2001

CHK D. BIEVENOUR 09OCT2001

APVD D. BIEVENOUR 09OCT2001

PRODUCT SPEC

108-20166

APPLICATION SPEC


114-20079

WEIGHT -

CUSTOMER DRAWING

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.3  
1 PLC ±.25  
2 PLC ±.25  
3 PLC ±.25  
4 PLC ±.25  
ANGLES ±.2

MATERIAL

FINISH



TE Connectivity

NAME  
TERMINAL BLOCK HEADER ASSEMBLY  
90 DEGREE, OPEN ENDS  
7.62mm PITCH

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779C-282965

SCALE 4:1 SHEET 1 OF 1 REV C1