

DWG. NO. SD-5279-NA

E





D

C
B
A
DIMENSIONS IN METRIC DO NOT SCALE DRAWING

1:MM

注記
NOTE

- △ 全極数が偶数の場合のみ適用。
TO BE APPLIED ONLY WHEN ALL CKTS. ARE EVEN.
- 2 ウエハーの反りは、長さ 25.4 に対して 0.2 最大。
CAMBER MUST BE 0.24 MAX.PER 25.4.



59.88	55.88	10-02-1127	5279-12A	12
54.8	50.8	↑ -1117	↑ -11A	11
49.72	45.72	↑ -1107	↑ -10A	10
44.64	40.64	↑ -1097	↑ -09A	9
39.56	35.56	↑ -1087	↑ -08A	8
34.48	30.48	↑ -1077	↑ -07A	7
29.4	25.4	↑ -1067	↑ -06A	6
24.32	20.32	↑ -1057	↑ -05A	5
19.24	15.24	↑ -1047	↑ -04A	4
14.16	10.16	↑ -1037	↑ -03A	3
9.08	5.08	10-02-1027	5279-02A	2
B	A	EDP NO.	ENG. NO.	極数 CKT.

角度	ANGLE	±3°				材料	図中参照
30 以上	OVER	±0.3				仕上げ	SEE DRAWING
10 以上 30 未満	OVER	±0.25				適用電線範囲	—H—
10 未満	UNDER	±0.2				被覆外径	—H—
一般公差	GENERAL TOLERANCES					INS. RANGE	—H—
記号	LTR	変更 & 再作図 (J40818)	T.A	H.H	9/10/5	DRAWN BY	CHK'D BY
REVISION	RECORD	REVISION	CHK	DATE		T.ASAKAWA	Y.M.H.HIRAMOTO
						APP'D BY	尺 度
						M.FUKUSHIMA	SCALE —H—

molex MOLEX-JAPAN CO.,LTD. 日本モレックス株式会社	
REVISE ONLY ON CAD SYSTEM	
TITLE 名称	
KK 5.08 WAFER ASS'Y	
DWG. NO.	REV
SD-5279-NA	A