




MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



NOTES:

- TUSONIX STANDARD PART NUMBER: 4251-001.
TUSONIX RoHS COMPLIANT PART NUMBER: 4251-001 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
- PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
- SUPPLIED WITH SILVER PLATED COPPER ALLOY HEX NUT AND INTERNAL TOOTH LOCK WASHER.

15,000	50 VDC	10 GΩ	250 VDC	10 A	5	9	18	45	65	70	70
MIN. CAP.(pf)	+125 °C DC WORKING VOLTAGE	I.R. MIN. @ 100 VDC	DWV	CURRENT	1 MHz	3 MHz	10 MHz	30 MHz	100 MHz	300 MHz	1GHz
MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220											
X-2015 Rev-0 REVISION RECORD	Original Release C.O. 6611	1 RDN TO COMP FMT. S.M. 06-03-02	2 20020528-3-02 DWV 250 WAS 125. S.M. 09-22-03	3 20030922-5-03 ADDED NOTES 1-3. S.M. 10-06-05	4 20050927-7-03	--TOLERANCES-- Unless Otherwise Specified			Title MULTI LAYER BUSHING STYLE EMI FILTER		
	HDIM'S REVISED .81 WAS .812 6.7 WAS 6.75. TITLE CHGD. E.C. 5-26-92					DECIMAL ± .031 [0.79]			Drawn S. M. 02-28-02		
	6667					ANGLES ±			Scale 4 X		
	20020528-3-02					Approved T.C. 02-58-02			A		
	20030922-5-03					TUSONIX TUCSON, ARIZONA			4251-001		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4251-001LF](#)