





▲ CIRCUIT DIAGRAM
ON - ON
SINGLE COLOR LED

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. TERMINAL NUMBERS FOR REF. ONLY
3. TOLERANCE: X.X=± 0.4
X.XX=± 0.25
4. RATING: 0.3A @ 6VDC
5. TRAVEL: 2.0 ±0.2
6. OPERATING FORCE: 200± 150gF
7. ELECTRICAL LIFE: 10,000 CYCLES MIN.
8. CONTACT RESISTANCE: 50mΩ MAX.
9. INSULATION RESISTANCE: 100MΩ AT 500 VDC
10. DIELECTRIC STRENGTH: 500VAC
11. OPERATING TEMPERATURE: -40C to +85C
12. ▲ DENOTES CRITICAL PARAMETER
13. 2002/95/EC (ROHS) COMPLIANT



▲ LED SPECS	UNITS	BLUE
FORWARD CURRENT	mA	20
FORWARD VOLTAGE @ 20mA	V	3.3 typ.-4.0 max.
LUMINOUS INTENSITY @ 20mA	mcd	100 typ.



TITLE EGL2290B

A	22349	New Release	6/10/2016	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 4:1	DATE 6/3/2016	DR rc	DWG B300002	REV A
--------------	------------------	----------	----------------	----------