

STANDARD CAPACITANCE TVS ARRAY

APPLICATIONS

- ✓ RS-485 Transceivers
- ✓ Network Interfaces
- ✓ Wireless Systems
- ✓ Portable Electronics

IEC COMPATIBILITY (EN61000-4)


- ✓ 61000-4-2 (ESD): Air - 15kV, Contact - 8kV
- ✓ 61000-4-4 (EFT): 40A - 5/50ns
- ✓ 61000-4-5 (Surge): 24A, 8/20 μ s - Level 2(Line-Ground) & Level 3(Line-Line)

FEATURES


- ✓ ESD Protection > 40 kilovolts
- ✓ 600 Watts Peak Pulse Power per Line ($t_p = 8/20\mu$ s)
- ✓ Asymmetrical Data Line Protection

MECHANICAL CHARACTERISTICS

- ✓ Molded JEDEC SOT-23
- ✓ Weight 0.6 grams (Approximate)
- ✓ Flammability rating UL 94V-0
- ✓ 8mm Tape and Reel Per EIA Standard 481
- ✓ Device Marking: Marking Code



PIN CONFIGURATION



DEVICE CHARACTERISTICS

MAXIMUM RATINGS @ 25°C Unless Otherwise Specified			
PARAMETER	SYMBOL	VALUE	UNITS
Peak Pulse Power ($t_p = 8/20\mu s$) - See Figure 1	P_{PP}	600	Watts
Operating Temperature	T_J	-55°C to 150°C	°C
Storage Temperature	T_{STG}	-55°C to 150°C	°C

ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified							
PART NUMBER (See Note 1)	DEVICE MARKING CODE (See Note 2)	RATED STAND-OFF VOLTAGE V_{WM} VOLTS	MINIMUM BREAKDOWN VOLTAGE @ 1mA $V_{(BR)}$ VOLTS	MAXIMUM CLAMPING VOLTAGE (See Fig. 2) @ $I_p = 1A$ V_C VOLTS	MAXIMUM CLAMPING VOLTAGE (See Fig. 2) @ 8/20 μs V_C @ I_{PP}	MAXIMUM LEAKAGE CURRENT @ V_{WM} I_D μA	TYPICAL CAPACITANCE @ 0V, 1 MHz C pF
Pin 3-1 & 3-2	712	7.0	7.5	11.0	17V @ 34A	20	75
Pin 1-3 & 2-3	712	12.0	13.3	19.0	30V @ 30A	1	75

Note 1: For 7V, pin 3 is positive. For 12V, pins 1 and 2 are positive.

Note 2: Marking code applies to same device.

GRAPHS

FIGURE 1
PEAK PULSE POWER VS PULSE TIME




FIGURE 2
PULSE WAVE FORM







FIGURE 3
POWER DERATING CURVE



PACKAGE OUTLINE & DIMENSIONS

PACKAGE OUTLINE 	SOT-23  PACKAGE DIMENSIONS <table><tr><th rowspan="2">DIM</th><th colspan="2">MILLIMETERS</th><th colspan="2">INCHES</th></tr><tr><th>MIN</th><th>MAX</th><th>MIN</th><th>MAX</th></tr><tr><td>A</td><td>2.80</td><td>3.04</td><td>0.1102</td><td>0.1197</td></tr><tr><td>B</td><td>1.20</td><td>1.40</td><td>0.0472</td><td>0.0551</td></tr><tr><td>C</td><td>0.89</td><td>1.11</td><td>0.0350</td><td>0.0440</td></tr><tr><td>D</td><td>0.37</td><td>0.50</td><td>0.0150</td><td>0.0200</td></tr><tr><td>G</td><td>1.78</td><td>2.04</td><td>0.0701</td><td>0.0807</td></tr><tr><td>H</td><td>0.013</td><td>0.100</td><td>0.0005</td><td>0.0040</td></tr><tr><td>J</td><td>0.085</td><td>0.177</td><td>0.0034</td><td>0.0070</td></tr><tr><td>K</td><td>0.45</td><td>0.60</td><td>0.0180</td><td>0.0236</td></tr><tr><td>L</td><td>0.89</td><td>1.02</td><td>0.0350</td><td>0.0401</td></tr><tr><td>S</td><td>2.10</td><td>2.50</td><td>0.0830</td><td>0.0984</td></tr><tr><td>V</td><td>0.45</td><td>0.60</td><td>0.0177</td><td>0.0236</td></tr></table>	DIM	MILLIMETERS		INCHES		MIN	MAX	MIN	MAX	A	2.80	3.04	0.1102	0.1197	B	1.20	1.40	0.0472	0.0551	C	0.89	1.11	0.0350	0.0440	D	0.37	0.50	0.0150	0.0200	G	1.78	2.04	0.0701	0.0807	H	0.013	0.100	0.0005	0.0040	J	0.085	0.177	0.0034	0.0070	K	0.45	0.60	0.0180	0.0236	L	0.89	1.02	0.0350	0.0401	S	2.10	2.50	0.0830	0.0984	V	0.45	0.60	0.0177	0.0236
DIM	MILLIMETERS		INCHES																																																														
	MIN	MAX	MIN	MAX																																																													
A	2.80	3.04	0.1102	0.1197																																																													
B	1.20	1.40	0.0472	0.0551																																																													
C	0.89	1.11	0.0350	0.0440																																																													
D	0.37	0.50	0.0150	0.0200																																																													
G	1.78	2.04	0.0701	0.0807																																																													
H	0.013	0.100	0.0005	0.0040																																																													
J	0.085	0.177	0.0034	0.0070																																																													
K	0.45	0.60	0.0180	0.0236																																																													
L	0.89	1.02	0.0350	0.0401																																																													
S	2.10	2.50	0.0830	0.0984																																																													
V	0.45	0.60	0.0177	0.0236																																																													
MOUNTING PAD 	NOTES 1. Dimensioning and tolerances per ANSI Y14.5M, 1985. 2. Controlling Dimension: Inches 3. Pin 3 is the cathode (Unidirectional Only). 4. Dimensions are exclusive of mold flash and metal burrs. TAPE & REEL ORDERING NOMENCLATURE 1. Surface mount product is taped and reeled in accordance with EIA-481. 2. Suffix -T7 = 7 Inch Reel - 3,000 pieces per 8mm tape, i.e., PSM712-T7. 3. Suffix -T13 = 13 Inch Reel - 10,000 pieces per 8mm tape, i.e., PSM712-T13. Outline & Dimensions: Rev 1 - 11/01, 06012																																																																

COPYRIGHT © ProTek Devices 2003

SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice (except JEDEC).

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice, and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance, ProTek assumes no responsibility with respect to the selection or specifications of such products.

ProTek Devices

2929 South Fair Lane, Tempe, AZ 85282

Tel: 602-431-8101 Fax: 602-431-2288

E-Mail: sales@protekdevices.com

Web Site: www.protekdevices.com