


**SURFACE MOUNT GLASS PASSIVATED  
 SUPER FAST SILICON RECTIFIER**

**VOLTAGE RANGE 50 to 400 Volts CURRENT 1.0 Ampere**

**FEATURES**

- \* Glass passivated device
- \* Ideal for surface mounted applications
- \* Low leakage current
- \* Metallurgically bonded construction
- \* Mounting position: Any
- \* Weight: 0.09 gram

**DO-214AA**



Dimensions in inches and (millimeters)

**MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS**

Ratings at 25 °C ambient temperature unless otherwise specified.  
 Single phase, half wave, 60 Hz, resistive or inductive load.  
 For capacitive load, derate current by 20%.

**MAXIMUM RATINGS** (At TA = 25°C unless otherwise noted)

| RATINGS                                                                                                                       | SYMBOL                            | EFM101B      | EFM102B | EFM103B | EFM104B | EFM105B | EFM106B | UNITS |
|-------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|--------------|---------|---------|---------|---------|---------|-------|
| Maximum Recurrent Peak Reverse Voltage                                                                                        | V <sub>RRM</sub>                  | 50           | 100     | 150     | 200     | 300     | 400     | Volts |
| Maximum RMS Volts                                                                                                             | V <sub>RMS</sub>                  | 35           | 70      | 105     | 140     | 210     | 280     | Volts |
| Maximum DC Blocking Voltage                                                                                                   | V <sub>DC</sub>                   | 50           | 100     | 150     | 200     | 300     | 400     | Volts |
| Maximum Average Forward Current<br>at T <sub>A</sub> = 55°C                                                                   | I <sub>O</sub>                    | 1.0          |         |         |         |         |         | Amps  |
| Peak Forward Surge Current I <sub>FM</sub> (surge): 8.3 ms single half<br>sine-wave superimposed on rated load (JEDEC method) | I <sub>FSM</sub>                  | 30           |         |         |         |         |         | Amps  |
| Typical Junction Capacitance (Note 2)                                                                                         | C <sub>J</sub>                    | 15           |         |         |         | 10      |         | pF    |
| Operating and Storage Temperature Range                                                                                       | T <sub>J</sub> , T <sub>STG</sub> | -65 to + 175 |         |         |         |         |         | °C    |

**ELECTRICAL CHARACTERISTICS** (At TA = 25°C unless otherwise noted)

| CHARACTERISTICS                        |                        | SYMBOL         | EFM101B | EFM102B | EFM103B | EFM104B | EFM105B | EFM106B | UNITS |
|----------------------------------------|------------------------|----------------|---------|---------|---------|---------|---------|---------|-------|
| Maximum Forward Voltage at 1.0A DC     |                        | V <sub>F</sub> | 0.95    |         |         |         | 1.25    |         | Volts |
| Maximum DC Reverse Current             | @T <sub>A</sub> = 25°C | I <sub>R</sub> | 5.0     |         |         |         |         |         | uAmps |
| at Rated DC Blocking Voltage           | @T <sub>A</sub> =100°C |                | 100     |         |         |         |         |         |       |
| Maximum Reverse Recovery Time (Note 1) |                        | trr            | 35      |         |         |         |         |         | nSec  |


NOTES : 1. Test Conditions: I<sub>F</sub>=0.5A, I<sub>R</sub>=1.0A, I<sub>RR</sub>=0.25A.

2. Measured at 1 MHz and applied reverse voltage of 4.0 volts.

2004-12

REV.A

## Mounting Pad Layout



Dimensions in inches and (millimeters)