

SLV SERIES

105°C Long Life, Lead Free Reflow Soldering.

◆FEATURES

- Load Life : 105°C 5000 hours.
- Lead free reflow soldering is available.
- Available for high density mounting.
- RoHS compliance.



◆SPECIFICATIONS

Items	Characteristics						
Category Temperature Range	-40~+105°C						
Rated Voltage Range	6.3~50V.DC						
Capacitance Tolerance	±20% (20°C, 120Hz)						
Leakage Current(MAX)	$I=0.01CV$ or $3\mu A$ whichever is greater. (After 2 minutes application of rated voltage) $I=$ Leakage Current(μA) $C=$ Capacitance(μF) $V=$ Rated Voltage(V)						
Dissipation Factor(MAX) (tanδ)	Rated Voltage (V)	6.3	10	16	25	35	50
	tanδ	0.30	0.24	0.20	0.16	0.14	0.14
Endurance	After applying rated voltage with rated ripple current for 5000 hours at 105°C, the capacitors shall meet the following requirements.						
	Capacitance Change	Within ±30% of the initial value.					
	Dissipation Factor	Not more than 300% of the specified value.					
	Leakage Current	Not more than the specified value.					
Low Temperature Stability Impedance Ratio(MAX)	Rated Voltage (V)	6.3	10	16	25	35	50
	$Z(-25^{\circ}C)/Z(20^{\circ}C)$	4	3	2	2	2	2
	$Z(-40^{\circ}C)/Z(20^{\circ}C)$	14	12	8	6	4	3

◆DIMENSIONS

(mm)

φD	L	A1	B1	C	W1	P
4	6.1	4.3	4.3	1.8	0.5~0.8	1.0
5	6.1	5.3	5.3	2.2	0.5~0.8	1.3
6.3	6.1	6.6	6.6	2.7	0.5~0.8	1.8

◆MARKING

※Voltage Code

Rated Voltage (V)	6.3	10	16	25	35	50
Rated Voltage code	j	A	C	E	V	H

◆MULTIPLIER FOR RIPPLE CURRENT

Frequency (Hz)	60 (50)	120	500	1k	10k≤
0.47~1μF	0.50	1.00	1.20	1.30	1.50
2.2~4.7μF	0.65	1.00	1.20	1.30	1.50
10~47μF	0.80	1.00	1.20	1.30	1.50
100μF	0.80	1.00	1.10	1.15	1.20

◆STANDARD SIZE

Size φD×L(mm), Ripple Current (mA r.m.s./105°C, 120Hz)

V.DC	Cap (μF)	Size (φD×L)	Rated Ripple Current
6.3 (0J)	22	4×6.1	22
	47	5×6.1	38
	100	6.3×6.1	69
10(1A)	33	5×6.1	35
16 (1C)	10	4×6.1	18
	22	5×6.1	30
	47	6.3×6.1	50

V.DC	Cap (μF)	Size (φD×L)	Rated Ripple Current
25(1E)	33	6.3×6.1	50
35 (1V)	4.7	4×6.1	16
	10	5×6.1	27
	22	6.3×6.1	44

V.DC	Cap (μF)	Size (φD×L)	Rated Ripple Current
50 (1H)	0.47	4×6.1	4
	1	4×6.1	8
	2.2	4×6.1	11
	3.3	4×6.1	14
	4.7	5×6.1	19
	10	6.3×6.1	32

◆PART NUMBER

□□□	SLV	□□□□□	M	□□□	D×L
Rated Voltage	Series	Capacitance	Capacitance Tolerance	Option	Case Size