

# MC14504B

## Hex Level Shifter for TTL to CMOS or CMOS to CMOS

The MC14504B is a hex non-inverting level shifter using CMOS technology. The level shifter will shift a TTL signal to CMOS logic levels for any CMOS supply voltage between 5 and 15 volts. A control input also allows interface from CMOS to CMOS at one logic level to another logic level: Either up or down level translating is accomplished by selection of power supply levels  $V_{DD}$  and  $V_{CC}$ . The  $V_{CC}$  level sets the input signal levels while  $V_{DD}$  selects the output voltage levels.

### Features

- UP Translates from a Low to a High Voltage or DOWN Translates from a High to a Low Voltage
- Input Threshold Can Be Shifted for TTL Compatibility
- No Sequencing Required on Power Supplies or Inputs for Power Up or Power Down
- 3 to 18 Vdc Operation for  $V_{DD}$  and  $V_{CC}$
- Diode Protected Inputs to  $V_{SS}$
- Capable of Driving Two Low-Power TTL Loads or One Low-Power Schottky TTL Load Over the Rated Temperature Range
- These Devices are Pb-Free and are RoHS Compliant
- NLV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable

### MAXIMUM RATINGS (Voltages Referenced to $V_{SS}$ )

| Symbol            | Parameter                                         | Value                  | Unit |
|-------------------|---------------------------------------------------|------------------------|------|
| $V_{CC}$          | DC Supply Voltage Range                           | -0.5 to +18.0          | V    |
| $V_{DD}$          | DC Supply Voltage Range                           | -0.5 to +18.0          | V    |
| $V_{in}$          | Input Voltage Range (DC or Transient)             | -0.5 to +18.0          | V    |
| $V_{out}$         | Output Voltage Range (DC or Transient)            | -0.5 to $V_{DD} + 0.5$ | V    |
| $I_{in}, I_{out}$ | Input or Output Current (DC or Transient) per Pin | $\pm 10$               | mA   |
| $P_D$             | Power Dissipation, per Package (Note 1)           | 500                    | mW   |
| $T_A$             | Ambient Temperature Range                         | -55 to +125            | °C   |
| $T_{stg}$         | Storage Temperature Range                         | -65 to +150            | °C   |
| $T_L$             | Lead Temperature (8-Second Soldering)             | 260                    | °C   |

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

#### 1. Temperature Derating:

Plastic "P and D/DW" Packages: -7.0 mW/°C From 65°C To 125°C

This device contains protection circuitry to guard against damage due to high static voltages or electric fields. However, precautions must be taken to avoid applications of any voltage higher than maximum rated voltages to this high-impedance circuit. For proper operation,  $V_{in}$  and  $V_{out}$  should be constrained to the range  $V_{SS} \leq (V_{in} \text{ or } V_{out}) \leq V_{DD}$ .


Unused inputs must always be tied to an appropriate logic voltage level (e.g., either  $V_{SS}$  or  $V_{DD}$ ). Unused outputs must be left open.





ON Semiconductor®

<http://onsemi.com>


### MARKING DIAGRAMS





PDIP-16  
P SUFFIX  
CASE 648




SOIC-16  
D SUFFIX  
CASE 751B



TSSOP-16  
DT SUFFIX  
CASE 948F



SOEIAJ-16  
F SUFFIX  
CASE 966



A = Assembly Location  
WL, L = Wafer Lot  
YY, Y = Year  
WW, W = Work Week  
G or ■ = Pb-Free Indicator

(Note: Microdot may be in either location)

### ORDERING INFORMATION


See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

# MC14504B

## PIN ASSIGNMENT

|                  |   |    |                  |
|------------------|---|----|------------------|
| V <sub>CC</sub>  | 1 | 16 | V <sub>DD</sub>  |
| A <sub>out</sub> | 2 | 15 | F <sub>out</sub> |
| A <sub>in</sub>  | 3 | 14 | F <sub>in</sub>  |
| B <sub>out</sub> | 4 | 13 | MODE             |
| B <sub>in</sub>  | 5 | 12 | E <sub>out</sub> |
| C <sub>out</sub> | 6 | 11 | E <sub>in</sub>  |
| C <sub>in</sub>  | 7 | 10 | D <sub>out</sub> |
| V <sub>SS</sub>  | 8 | 9  | D <sub>in</sub>  |

## LOGIC DIAGRAM



| Mode Select          | Input Logic Levels | Output Logic Levels |
|----------------------|--------------------|---------------------|
| 1 (V <sub>CC</sub> ) | TTL                | CMOS                |
| 0 (V <sub>SS</sub> ) | CMOS               | CMOS                |

1/6 of package shown.

## ORDERING INFORMATION

| Device          | Package                | Shipping <sup>†</sup>    |
|-----------------|------------------------|--------------------------|
| MC14504BCPG     | PDIP-16<br>(Pb-Free)   | 500 Units / Rail         |
| MC14504BDG      | SOIC-16<br>(Pb-Free)   | 48 Units / Rail          |
| NLV14504BDG*    |                        |                          |
| MC14504BDR2G    | SOIC-16<br>(Pb-Free)   | 2500 Units / Tape & Reel |
| NLV14504BDR2G*  |                        |                          |
| MC14504BDTG     | TSSOP-16<br>(Pb-Free)  | 96 Units / Rail          |
| NLV14504BDTG*   |                        |                          |
| MC14504BDTR2G   | TSSOP-16<br>(Pb-Free)  | 2500 Units / Tape & Reel |
| NLV14504BDTR2G* |                        |                          |
| MC14504BFG      | SOEIAJ-16<br>(Pb-Free) | 50 Units / Rail          |
| MC14504BFELG    | SOEIAJ-16<br>(Pb-Free) | 2000 Units / Tape & Reel |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

\*NLV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q100 Qualified and PPAP Capable.

# MC14504B

## ELECTRICAL CHARACTERISTICS (Voltages Referenced to V<sub>SS</sub>)

| Characteristic                                                                                                                                                                                                                                                 | Symbol                                | V <sub>CC</sub><br>Vdc | V <sub>DD</sub><br>Vdc | - 55°C |       | 25°C  |                 |       | 125°C |       | Unit |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------|------------------------|------------------------|--------|-------|-------|-----------------|-------|-------|-------|------|
|                                                                                                                                                                                                                                                                |                                       |                        |                        | Min    | Max   | Min   | Typ<br>(Note 2) | Max   | Min   | Max   |      |
| Output Voltage<br>V <sub>in</sub> = 0 V<br><br>V <sub>in</sub> = V <sub>CC</sub>                                                                                                                                                                               | “0” Level<br><br>V <sub>OL</sub>      | –                      | 5.0                    | –      | 0.05  | –     | 0               | 0.05  | –     | 0.05  | Vdc  |
|                                                                                                                                                                                                                                                                |                                       | –                      | 10                     | –      | 0.05  | –     | 0               | 0.05  | –     | 0.05  |      |
|                                                                                                                                                                                                                                                                |                                       | –                      | 15                     | –      | 0.05  | –     | 0               | 0.05  | –     | 0.05  |      |
|                                                                                                                                                                                                                                                                | “1” Level<br><br>V <sub>OH</sub>      | –                      | 5.0                    | 4.95   | –     | 4.95  | 5.0             | –     | 4.95  | –     | Vdc  |
|                                                                                                                                                                                                                                                                |                                       | –                      | 10                     | 9.95   | –     | 9.95  | 10              | –     | 9.95  | –     |      |
|                                                                                                                                                                                                                                                                |                                       | –                      | 15                     | 14.95  | –     | 14.95 | 15              | –     | 14.95 | –     |      |
| Input Voltage<br>“0” Level<br>(V <sub>OL</sub> = 1.0 Vdc) TTL–CMOS<br>(V <sub>OL</sub> = 1.5 Vdc) TTL–CMOS<br>(V <sub>OL</sub> = 1.0 Vdc) CMOS–CMOS<br>(V <sub>OL</sub> = 1.5 Vdc) CMOS–CMOS<br>(V <sub>OL</sub> = 1.5 Vdc) CMOS–CMOS                          | V <sub>IL</sub>                       | 5.0                    | 10                     | –      | 0.8   | –     | 1.3             | 0.8   | –     | 0.8   | Vdc  |
|                                                                                                                                                                                                                                                                |                                       | 5.0                    | 15                     | –      | 0.8   | –     | 1.3             | 0.8   | –     | 0.8   |      |
|                                                                                                                                                                                                                                                                |                                       | 5.0                    | 10                     | –      | 1.5   | –     | 2.25            | 1.5   | –     | 1.4   |      |
|                                                                                                                                                                                                                                                                |                                       | 5.0                    | 15                     | –      | 1.5   | –     | 2.25            | 1.5   | –     | 1.5   |      |
|                                                                                                                                                                                                                                                                |                                       | 10                     | 15                     | –      | 3.0   | –     | 4.5             | 3.0   | –     | 2.9   |      |
|                                                                                                                                                                                                                                                                |                                       | –                      | –                      | –      | –     | –     | –               | –     | –     | –     |      |
| Input Voltage<br>“1” Level<br>(V <sub>OH</sub> = 9.0 Vdc) TTL–CMOS<br>(V <sub>OH</sub> = 13.5 Vdc) TTL–CMOS<br>(V <sub>OH</sub> = 9.0 Vdc) CMOS–CMOS<br>(V <sub>OH</sub> = 13.5 Vdc) CMOS–CMOS<br>(V <sub>OH</sub> = 13.5 Vdc) CMOS–CMOS                       | V <sub>IH</sub>                       | 5.0                    | 10                     | 2.0    | –     | 2.0   | 1.5             | –     | 2.0   | –     | Vdc  |
|                                                                                                                                                                                                                                                                |                                       | 5.0                    | 15                     | 2.0    | –     | 2.0   | 1.5             | –     | 2.0   | –     |      |
|                                                                                                                                                                                                                                                                |                                       | 5.0                    | 10                     | 3.6    | –     | 3.5   | 2.75            | –     | 3.5   | –     |      |
|                                                                                                                                                                                                                                                                |                                       | 5.0                    | 15                     | 3.6    | –     | 3.5   | 2.75            | –     | 3.5   | –     |      |
|                                                                                                                                                                                                                                                                |                                       | 10                     | 15                     | 7.1    | –     | 7.0   | 5.5             | –     | 7.0   | –     |      |
|                                                                                                                                                                                                                                                                |                                       | –                      | –                      | –      | –     | –     | –               | –     | –     | –     |      |
| Output Drive Current<br>(V <sub>OH</sub> = 2.5 Vdc) Source<br>(V <sub>OH</sub> = 4.6 Vdc)<br>(V <sub>OH</sub> = 9.5 Vdc)<br>(V <sub>OH</sub> = 13.5 Vdc)<br><br>(V <sub>OL</sub> = 0.4 Vdc) Sink<br>(V <sub>OL</sub> = 0.5 Vdc)<br>(V <sub>OL</sub> = 1.5 Vdc) | I <sub>OH</sub>                       | –                      | 5.0                    | –3.0   | –     | –2.4  | –4.2            | –     | –1.7  | –     | mAdc |
|                                                                                                                                                                                                                                                                |                                       | –                      | 5.0                    | –0.64  | –     | –0.51 | –0.88           | –     | –0.36 | –     |      |
|                                                                                                                                                                                                                                                                |                                       | –                      | 10                     | –1.6   | –     | –1.3  | –2.25           | –     | –0.9  | –     |      |
|                                                                                                                                                                                                                                                                |                                       | –                      | 15                     | –4.2   | –     | –3.4  | –8.8            | –     | –2.4  | –     |      |
|                                                                                                                                                                                                                                                                | I <sub>OL</sub>                       | –                      | 5.0                    | 0.64   | –     | 0.51  | 0.88            | –     | 0.36  | –     | mAdc |
|                                                                                                                                                                                                                                                                |                                       | –                      | 10                     | 1.6    | –     | 1.3   | 2.25            | –     | 0.9   | –     |      |
|                                                                                                                                                                                                                                                                |                                       | –                      | 15                     | 4.2    | –     | 3.4   | 8.8             | –     | 2.4   | –     |      |
| Input Current                                                                                                                                                                                                                                                  | I <sub>in</sub>                       | –                      | 15                     | –      | ± 0.1 | –     | ± 0.00001       | ± 0.1 | –     | ± 1.0 | μAdc |
| Input Capacitance (V <sub>in</sub> = 0)                                                                                                                                                                                                                        | C <sub>in</sub>                       | –                      | –                      | –      | –     | –     | 5.0             | 7.5   | –     | –     | pF   |
| Quiescent Current<br>(Per Package)<br>CMOS–CMOS Mode                                                                                                                                                                                                           | I <sub>DD</sub> or<br>I <sub>CC</sub> | –                      | 5.0                    | –      | 0.05  | –     | 0.0005          | 0.05  | –     | 1.5   | μAdc |
|                                                                                                                                                                                                                                                                |                                       | –                      | 10                     | –      | 0.10  | –     | 0.0010          | 0.10  | –     | 3.0   |      |
|                                                                                                                                                                                                                                                                |                                       | –                      | 15                     | –      | 0.20  | –     | 0.0015          | 0.20  | –     | 6.0   |      |
| Quiescent Current<br>(Per Package)<br>TTL–CMOS Mode                                                                                                                                                                                                            | I <sub>DD</sub>                       | 5.0                    | 5.0                    | –      | 0.5   | –     | 0.0005          | 0.5   | –     | 3.8   | μAdc |
|                                                                                                                                                                                                                                                                |                                       | 5.0                    | 10                     | –      | 1.0   | –     | 0.0010          | 1.0   | –     | 7.5   |      |
|                                                                                                                                                                                                                                                                |                                       | 5.0                    | 15                     | –      | 2.0   | –     | 0.0015          | 2.0   | –     | 15    |      |
| Quiescent Current<br>(Per Package)<br>TTL–CMOS Mode                                                                                                                                                                                                            | I <sub>CC</sub>                       | 5.0                    | 5.0                    | –      | 5.0   | –     | 2.5             | 5.0   | –     | 6.0   | mAdc |
|                                                                                                                                                                                                                                                                |                                       | 5.0                    | 10                     | –      | 5.0   | –     | 2.5             | 5.0   | –     | 6.0   |      |
|                                                                                                                                                                                                                                                                |                                       | 5.0                    | 15                     | –      | 5.0   | –     | 2.5             | 5.0   | –     | 6.0   |      |

2. Data labelled “Typ” is not to be used for design purposes but is intended as an indication of the IC’s potential performance.

# MC14504B

## SWITCHING CHARACTERISTICS ( $C_L = 50 \text{ pF}$ , $T_A = 25^\circ\text{C}$ )

| Characteristic                    | Symbol                              | Shifting Mode                     | V <sub>CC</sub><br>Vdc            | V <sub>DD</sub><br>Vdc | Limits |                 |     | Unit |     |
|-----------------------------------|-------------------------------------|-----------------------------------|-----------------------------------|------------------------|--------|-----------------|-----|------|-----|
|                                   |                                     |                                   |                                   |                        | Min    | Typ<br>(Note 3) | Max |      |     |
| Propagation Delay, High to Low    | t <sub>PHL</sub>                    | TTL – CMOS                        | 5.0                               | 10                     | –      | 140             | 280 | ns   |     |
|                                   |                                     | V <sub>DD</sub> > V <sub>CC</sub> | 5.0                               | 15                     | –      | 140             | 280 |      |     |
|                                   |                                     | CMOS – CMOS                       | 5.0                               | 10                     | –      | 120             | 240 |      |     |
|                                   |                                     |                                   | V <sub>DD</sub> > V <sub>CC</sub> | 5.0                    | 15     | –               | 120 |      | 240 |
|                                   |                                     |                                   | 10                                | 15                     | –      | 70              | 140 |      |     |
|                                   |                                     | CMOS – CMOS                       | 10                                | 5.0                    | –      | 185             | 370 |      |     |
| V <sub>CC</sub> > V <sub>DD</sub> | 15                                  |                                   | 5.0                               | –                      | 185    | 370             |     |      |     |
| 15                                | 10                                  |                                   | –                                 | 175                    | 350    |                 |     |      |     |
| Propagation Delay, Low to High    | t <sub>PLH</sub>                    | TTL – CMOS                        | 5.0                               | 10                     | –      | 170             | 340 | ns   |     |
|                                   |                                     | V <sub>DD</sub> > V <sub>CC</sub> | 5.0                               | 15                     | –      | 160             | 320 |      |     |
|                                   |                                     | CMOS – CMOS                       | 5.0                               | 10                     | –      | 170             | 340 |      |     |
|                                   |                                     |                                   | V <sub>DD</sub> > V <sub>CC</sub> | 5.0                    | 15     | –               | 170 |      | 340 |
|                                   |                                     |                                   | 10                                | 15                     | –      | 100             | 200 |      |     |
|                                   |                                     | CMOS – CMOS                       | 10                                | 5.0                    | –      | 275             | 550 |      |     |
| V <sub>CC</sub> > V <sub>DD</sub> | 15                                  |                                   | 5.0                               | –                      | 275    | 550             |     |      |     |
| 15                                | 10                                  |                                   | –                                 | 145                    | 290    |                 |     |      |     |
| Output Rise and Fall Time         | t <sub>TLH</sub> , t <sub>THL</sub> | ALL                               | –                                 | 5.0                    | –      | 100             | 200 | ns   |     |
|                                   |                                     | –                                 | –                                 | 10                     | –      | 50              | 100 |      |     |
|                                   |                                     | –                                 | –                                 | 15                     | –      | 40              | 80  |      |     |

3. Data labelled “Typ” is not to be used for design purposes but is intended as an indication of the IC’s potential performance.




Figure 1. Input Switchpoint CMOS to CMOS Mode




Figure 2. Input Switchpoint TTL to CMOS Mode




Figure 3. Operating Boundary CMOS to CMOS Mode





Figure 4. Operating Boundary TTL to CMOS Mode

# MC14504B

## PACKAGE DIMENSIONS

PDIP-16  
P SUFFIX  
PLASTIC DIP PACKAGE  
CASE 648-08  
ISSUE T




### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. DIMENSION L TO CENTER OF LEADS WHEN FORMED PARALLEL.
4. DIMENSION B DOES NOT INCLUDE MOLD FLASH.
5. ROUNDED CORNERS OPTIONAL.

| DIM | INCHES    |       | MILLIMETERS |       |
|-----|-----------|-------|-------------|-------|
|     | MIN       | MAX   | MIN         | MAX   |
| A   | 0.740     | 0.770 | 18.80       | 19.55 |
| B   | 0.250     | 0.270 | 6.35        | 6.85  |
| C   | 0.145     | 0.175 | 3.69        | 4.44  |
| D   | 0.015     | 0.021 | 0.39        | 0.53  |
| F   | 0.040     | 0.70  | 1.02        | 1.77  |
| G   | 0.100 BSC |       | 2.54 BSC    |       |
| H   | 0.050 BSC |       | 1.27 BSC    |       |
| J   | 0.008     | 0.015 | 0.21        | 0.38  |
| K   | 0.110     | 0.130 | 2.80        | 3.30  |
| L   | 0.295     | 0.305 | 7.50        | 7.74  |
| M   | 0°        | 10°   | 0°          | 10°   |
| S   | 0.020     | 0.040 | 0.51        | 1.01  |

SOEIAJ-16  
F SUFFIX  
PLASTIC EIAJ SOIC PACKAGE  
CASE 966-01  
ISSUE A



### NOTES:


1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.
3. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH OR PROTRUSIONS AND ARE MEASURED AT THE PARTING LINE. MOLD FLASH OR PROTRUSIONS SHALL NOT EXCEED 0.15 (0.006) PER SIDE.
4. TERMINAL NUMBERS ARE SHOWN FOR REFERENCE ONLY.
5. THE LEAD WIDTH DIMENSION (b) DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.08 (0.003) TOTAL IN EXCESS OF THE LEAD WIDTH DIMENSION AT MAXIMUM MATERIAL CONDITION. DAMBAR CANNOT BE LOCATED ON THE LOWER RADIUS OR THE FOOT. MINIMUM SPACE BETWEEN PROTRUSIONS AND ADJACENT LEAD TO BE 0.46 (0.018).

| DIM            | MILLIMETERS |       | INCHES    |       |
|----------------|-------------|-------|-----------|-------|
|                | MIN         | MAX   | MIN       | MAX   |
| A              | ---         | 2.05  | ---       | 0.081 |
| A <sub>1</sub> | 0.05        | 0.20  | 0.002     | 0.008 |
| b              | 0.35        | 0.50  | 0.014     | 0.020 |
| c              | 0.10        | 0.20  | 0.007     | 0.011 |
| D              | 9.90        | 10.50 | 0.390     | 0.413 |
| E              | 5.10        | 5.45  | 0.201     | 0.215 |
| e              | 1.27 BSC    |       | 0.050 BSC |       |
| H <sub>E</sub> | 7.40        | 8.20  | 0.291     | 0.323 |
| L              | 0.50        | 0.85  | 0.020     | 0.033 |
| L <sub>E</sub> | 1.10        | 1.50  | 0.043     | 0.059 |
| M              | 0°          | 10°   | 0°        | 10°   |
| Q <sub>1</sub> | 0.70        | 0.90  | 0.028     | 0.035 |
| Z              | ---         | 0.78  | ---       | 0.031 |


# MC14504B

## PACKAGE DIMENSIONS

**TSSOP-16**  
**DT SUFFIX**  
 PLASTIC TSSOP PACKAGE  
 CASE 948F-01  
 ISSUE B




## SOLDERING FOOTPRINT



# MC14504B

## PACKAGE DIMENSIONS

### SOIC-16 D SUFFIX PLASTIC SOIC PACKAGE CASE 751B-05 ISSUE K




#### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.
3. DIMENSIONS A AND B DO NOT INCLUDE MOLD PROTRUSION.
4. MAXIMUM MOLD PROTRUSION 0.15 (0.006) PER SIDE.
5. DIMENSION D DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.127 (0.005) TOTAL IN EXCESS OF THE D DIMENSION AT MAXIMUM MATERIAL CONDITION.

| DIM | MILLIMETERS |       | INCHES    |       |
|-----|-------------|-------|-----------|-------|
|     | MIN         | MAX   | MIN       | MAX   |
| A   | 9.80        | 10.00 | 0.386     | 0.393 |
| B   | 3.80        | 4.00  | 0.150     | 0.157 |
| C   | 1.35        | 1.75  | 0.054     | 0.068 |
| D   | 0.35        | 0.49  | 0.014     | 0.019 |
| F   | 0.40        | 1.25  | 0.016     | 0.049 |
| G   | 1.27 BSC    |       | 0.050 BSC |       |
| J   | 0.19        | 0.25  | 0.008     | 0.009 |
| K   | 0.10        | 0.25  | 0.004     | 0.009 |
| M   | 0°          | 7°    | 0°        | 7°    |
| P   | 5.80        | 6.20  | 0.229     | 0.244 |
| R   | 0.25        | 0.50  | 0.010     | 0.019 |

## SOLDERING FOOTPRINT



ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor  
P.O. Box 5163, Denver, Colorado 80217 USA  
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
Email: [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

N. American Technical Support: 800-282-9855 Toll Free  
USA/Canada  
Europe, Middle East and Africa Technical Support:  
Phone: 421 33 790 2910  
Japan Customer Focus Center  
Phone: 81-3-5817-1050

ON Semiconductor Website: [www.onsemi.com](http://www.onsemi.com)

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative