



NOTES:

1. ALL DIMENSION IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
5. CONTACT RATING (NON-SWITCHING) 5A
6. OPERATING FORCE: 425 ± 100 CM/STANDARD
7. OPERATING TEMP: -30°C to 85°C
8. CIRCUIT SP: 6 POSITIONS, 60° INDEX.
9. DIELECTRIC STRENGTH 1000V RMS min. @ SEA LEVEL
10. DESIGNATE MAJOR DIMENSIONS
11. SUPPLIED HARDWARE: LOCK NUT AND WASHER (NOT




CONTACT CONFIGURATION

Timing: Non-Shorting



TERMINATION DETAIL

SCALE 2X



				
TITLE				
KC-60-A (9.5mm) 01-N-L-S				
SCALE		DATE	DR	DWG
1.5:1		12/5/02	CJB	G510595
				REV
				A