




Micro-D Sav-Con® Connector Savers Metal Shell



Micro-D Uni-Savers are ideal for applications in need of a connector saver for protection of test equipment. The unique one piece design reduces space requirements and mechanical stress.

- **Small Profile**
- **One-Piece Aluminum Shell**
- **EMI-Protected**
- **9 Through 100 Contacts**
- **Jacking Hardware Included**



HOW TO ORDER

Conn. Series	Shell Plating Table III*	Insert Material Table I*	No. of Contacts	Connector Type	Hardware
MWDM	1 – Cadmium	L – LCP (Liquid Crystal Polymer)	9	US (Uni-Saver)	P1 Combination Jackscrew and Jackpost (Provided Unassembled)
	2 – Nickel		15		
	4 – Black Anodize		21		
	5 – Gold		25		
	6 – Chem Film		31		
			37		
			51		
			100		
Sample Part Number:					
MWDM	5	L	— 25	US	P1
* SEE INSIDE BACK COVER FOLD-OUT FOR COMPLETE INFORMATION					

DIMENSIONS

Contacts	A		B	
	± .010	(0.3)	± .003	(0.1)
9	.775	(19.7)	.565	(14.4)
15	.925	(23.5)	.715	(18.2)
21	1.075	(27.3)	.865	(22.0)
25	1.175	(29.8)	.965	(24.5)
31	1.325	(33.7)	1.115	(28.3)
37	1.475	(37.5)	1.265	(32.1)
51	1.425	(36.2)	1.215	(30.9)
100	2.160	(54.9)	1.800	(45.7)
Contacts	C		D	
	± .010	(0.3)	Thread	
9	.298	(7.6)	#2-56 UNC	
15	.298	(7.6)	#2-56 UNC	
21	.298	(7.6)	#2-56 UNC	
25	.298	(7.6)	#2-56 UNC	
31	.298	(7.6)	#2-56 UNC	
37	.298	(7.6)	#2-56 UNC	
51	.341	(8.7)	#2-56 UNC	
100	.384	(9.8)	#4-40 UNC	

Metric dimensions (mm) are indicated in parentheses.