





MATERIAL NUMBER	OLD PART NUMBER	FINISHED LENGTH
130013-0515	1R5006A24A120	12.00" +1.75" -0 [1.3M +44.5 -0]



MALE FACE VIEW

1	RED WITH #1
2	RED WITH #2
3	GREEN-GND
4	RED WITH #4
5	RED WITH #5

WIRING DIAGRAM



KNOCKOUT HOLE

VOLTAGE RATING	600 VAC/VDC
AMPERAGE RATING	8 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 105°C
UL CERTIFICATIONS	UL LISTED, FILE NO. E258922
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	PVC	YELLOW
2	CONTACT PIN	COPPER ALLOY	GOLD OVER NICKEL
3	RECEPTACLE SHELL	ZINC DIE CAST	BLACK E-COATED
4	CONDUCTOR - 16 AWG. 26 x #30 COPPER STRANDING, 600V	PVC	SEE WIRING DIAGRAM
5	FLAG LABEL	PLASTIC FILM	BLACK/YELLOW

RLSD DRAWING EC NO: WNA2010-0425 DRWN: BWOODMAN2010/01/08 CH'KD: TW APPR: JFMURPHY 2010/01/14 A	DESCRIPTION REV	QUALITY SYMBOL ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY	DATE	TITLE MINI-CHANGE RECEPTACLE 5 POLE MALE 1/2 NPT AUTO CODE MOLEX INCORPORATED				
			4 PLACES	±---	±---	----	----					
			3 PLACES	±---	±.005	CHECKED BY	DATE					
			2 PLACES	±0.13	±.010	TW	2010/01/08					
			1 PLACE	±0.25	±.020	APPROVED BY	DATE					
			ANGULAR ±1/2°			JFMURPHY	2010/01/14	MOLEX	DOCUMENT NO. SD-130013-024		SHEET NO. 1 OF 1	
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE CHART			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
						SIZE C						