



8			7		
THIS DRAWING IS UNPUBLISHED.			RELEASED FOR PUBLICATION		
20			20		
© COPYRIGHT 20			BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.		
PART NUMBER	REV	FIRST USED	POWER UNIT	FEED TYPE	DESCRIPTION
1855289-1	B	122500-1	LEADMAKER	AIR FEED	CUTS CARRIER
1855289-2	A	565435-5	BENCH MODEL K	AIR FEED	CUTS CARRIER
1855289-3	A	354500-1	BENCH MODEL G	AIR FEED	CUTS CARRIER
7-1855289-7	A	-	-	-	SPARE PARTS

- △1 RECOMMENDED SPARE PARTS
- △2 GREASE LIGHTLY
- △3 GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE
- △4 INSTALL ITEMS 101, 102, & 119 ON SIDE OF STRIPPER ON APPL HOUSING USING ITEM 21.
- △5 FOR LARGE INSULATION DIAMETER PER TERMINAL MANUFACTURER .043-.067[1.09-1.70mm].

* WARNING
ON INSTALLATION, SET WIRE DISC TO LARGEST WIRE SIZE SETTING. USE OF SETTINGS BELOW MIN. REQUIRED CRIMP HEIGHT SETTING WILL CAUSE DAMAGE TO CRIMP TOOLING.




TERMINAL NAME: KK® Crimp Terminal					
TE P/N	MOLEX P/N	MOLEX TERMINAL - MOLEX CRIMP SPECS			
286698-1	08-50-0113	SEE CRIMP HEIGHTS TABLES ON SHEET 2			
286698-2	08-55-0101				
286698-3	08-56-0109				
286698-4	08-52-0101				
286698-5	08-65-0815				
286698-6	08-65-0813				
286698-7	97-00-0444	CRIMP	SIZE	TYPE	RANGE
1949741-1	08-70-0048				
1949741-2	08-70-0064	WIRE	.054 [1.37mm]	F	SEE SHEET 2
-	-	INSUL	.077 [1.96mm]	F	SEE SHEET 2
WIRE STRIP LENGTH 100 - 125 [2.54-3.18mm]	TERM APPL SPEC NONE	FEED 900 [5.08mm]	APPLICATOR INSTRUCTIONS 408-8040		SET UP GAGE 458637-1




LOC		DIST		REVISONS			
A		66		P	LTR	DESCRIPTION	DATE
				B1	ECR-12-013912		03AUG2012
							L.Z
							S.X

△4	-	1	1	1	-	1-22281-8	SPRING, COMPRESSION	121
-	42	21	42	IN	-	27319-4	TUBING,POLY-FLO, NATURAL	119
-	-	REF	-	-	-	692655-6	AIR FEED VALVE ASSEMBLY	118
-	1	1	1	-	-	461062-1	FEED FINGER ASSEMBLY	117
△3	-	REF	-	..	-	455749-1	GUARD WINDOW	116
△3	-	REF	-	..	-	679532-1	INSERT, GUARD	115
-	1	1	1	-	-	3-21001-5	SCR, SKT HD CAP 3/8-16 X 1.000	111
-	1	1	1	-	-	459610-1	MOUNT, FEED BRACKET	110
-	1	1	1	-	-	21024-8	WASHER, SPRG LOCK, REG 3/8	109
-	1	-	1	-	-	692655-7	AIR FEED VALVE ASSEMBLY	108
-	-	REF	-	-	-	24024-2	VALVE, SHUT OFF	106
-	-	1	-	-	-	692655-5	AIR FEED VALVE ASSEMBLY	105
-	1	1	1	-	-	461065-1	ASSEMBLY, AIR FEED	104
-	2	2	2	-	-	3-21000-9	SCR, SKT HD CAP 10-32 X 1.000	103
△4	-	1	1	1	-	986220-3	CLAMP, CABLE, BLACK	102
△4	-	1	-	1	-	23238-1	INSERT, COUPLING	101
-	2	2	2	-	-	2-21002-1	SCR, BTN SKT HD CAP 8-32 X .375	98
-	1	1	1	-	-	2-690712-4	FRONT STRIP GUIDE	96
-	2	2	2	-	-	1-21000-4	SCR, SKT HD CAP 4-40 X .375	95
-	1	1	1	-	-	8-21000-7	SCR, SKT HD CAP 10-32 X 2.500	93
-	1	1	1	-	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	88
-	1	1	1	-	-	1-455888-3	SPACER, CRIMPER	82
-	2	2	2	-	-	1-21002-4	SCR, BTN SKT HD CAP 4-40 X .375	79
-	1	1	1	-	-	1-189807-5	FENCE	78
-	1	1	1	-	-	4088040	SF APPL INST 408-8040	72
-	1	1	1	-	-	217238-1	GENERAL INSTRUCTION PKG	71
-	2	2	2	-	-	21024-2	WASHER, SPRG LOCK, REG NO 4	68
-	1	1	1	-	-	461264-5	PLATE, IDENTIFICATION	67
-	2	2	2	-	-	21017-2	SCREW, DRIVE	66
-	1	1	1	-	-	21009-2	SCR, SET, SELF LOCKING 1/4-20 X .250	63
-	2	2	2	-	-	5-21006-6	SCR, SET, CUP POINT 10-32 X .750	61
-	1	1	1	-	-	22733-8	SCR, BHSC, SELF-LOCKING, 8-32 X .375	60
-	1	1	1	-	-	2-22603-0	SCR, HEX HD CAP 8-32 X .312	59
-	1	1	1	-	-	3-694433-7	FEED PAWL	56
-	2	2	2	-	-	3-21000-0	SCR, SKT HD CAP 8-32 X .875	53
-	1	1	1	-	-	1583893-8	HOLDER, SLUG BLADE	50
-	1	1	1	-	-	1633399-1	APPL., BASIC AIR FEED SUB ASSY	46
-	1	1	1	-	-	690191-1	PLUG,NYLON	45
-	1	1	1	-	-	455673-6	RAM, SIDE FEED	44
-	1	1	1	-	-	7-21002-9	SCR, BTN SKT HD CAP 5/16-24 X 1.00	41
-	1	1	1	-	-	690125-1	SHIM SUB-ASSY	39
-	1	1	1	-	-	469367-7	SHIM	38
-	1	1	1	-	-	879103-3	FINE ADJUST HEAD ASSEMBLY	37
-	2	2	2	-	-	2-21002-4	SCR, BTN SKT HD CAP 8-32 X .750	33
-	3	3	3	-	-	21024-5	WASHER, SPRG LOCK, REG NO 10	32
-	1	1	1	-	-	3-21000-4	SCR, SKT HD CAP 10-32 X .375	31
-	1	1	1	-	-	1320908-5	SPACER, STRIP GUIDE	30
-	1	1	1	-	-	1-1633087-1	PLATE, STRIP GUIDE	29
-	2	2	2	-	-	8-22281-7	SPRING, COMPRESSION	27
-	1	1	1	-	-	356835-1	LEVER, DRAG RELEASE	26
-	1	1	1	-	-	5-690754-2	DRAG, SPECIAL	25
-	1	1	1	-	-	1-1320928-0	STRIP GUIDE	24
-	1	1	1	-	-	22353-8	SCR, SHLD, SLOT HD, 3/16 DIA	23
-	1	1	1	-	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	21
-	2	2	2	-	-	21024-4	WASHER, SPRG LOCK, REG NO 8	20
-	1	1	1	-	-	1-456468-4	STRIPPER, SPECIAL	19
△1	-	1	1	1	-	1633578-2	PLATE, REAR SHEAR	15
-	-	-	-	..	-	-	-	13
-	-	-	-	..	-	-	-	12
△1	-	1	1	1	-	1633579-2	BLADE, SLUG	10
-	-	-	-	..	-	-	-	9
△1	1	1	1	1	-	1633610-1	ANVIL, SPECIAL	8
-	-	-	-	..	-	-	-	7
-	-	-	-	..	-	-	-	6
-	1	1	1	-	-	4-240641-9	SPACER	5
-	1	1	1	-	-	3-238009-5	BLOCK, FL CRIMPER SPACER	4
△1	1	1	1	1	-	1633511-8	CRIMPER, INSULATION F	3
△1	-	1	1	1	-	455888-2	SPACER, CRIMPER	2
△1	1	1	1	1	-	2-1633305-2	CRIMPER, WIRE PREMIUM	1
-77	-3	-2	-1	U/M	PART NO	DESCRIPTION		ITEM NO



AMP 4805 REV 31MAR2000




THIS DRAWING IS A CONTROLLED DOCUMENT FOR PROTECTING THE PROPRIETARY INFORMATION OF THE COMPANY AND ITS SUBSIDIARIES. IT IS UNPUBLISHED AND NOT TO BE RELEASED OR DISCLOSED TO THE PUBLIC OR TO OTHERS WITHOUT THE WRITTEN PERMISSION OF THE COMPANY.		OWN R. KNEPPER 16 JAN 2008		TE Connectivity Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		APVD N. DEMING 16 JAN 2008		NAME FINE ADJUST SIDE FEED HDM APPLICATOR	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.001 1 PLC ±.01 2 PLC ±.01 3 PLC ±.001 4 PLC ±.0001 ANGLES ±		PRODUCT SPEC		SIZE A	
MATERIAL		APPLICATION SPEC		CAGE CODE 00779	
FINISH		WEIGHT		DRAWING NO 1855289	
CUSTOMER DRAWING		SCALE 3:5		SHEET 1 OF 2	
				REV B1	



CUSTOMER VIEWABLE ASSEMBLY

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.		

[illegible]

TERMINAL NAME: RK® Crimp Terminal							
TE P/N	MOLEX P/N	MOLEX TERMINAL - MOLEX CRIMP SPECS				REF SETTING	
286698-1	08-50-0113	CRIMP HEIGHT			WIRE SIZE		
286698-2	08-55-0101						
286698-3	08-56-0109	.032±.001[0.81±0.03mm]			22AWG or 0.35mm ²		B8
-	-	.030±.001[0.76±0.03mm]			24AWG or 0.20mm ²		C2
-	-	.029±.001[0.74±0.03mm]			26AWG or 0.12mm ²		C2
-	-	.028±.001[0.71±0.03mm]			28AWG or 0.08mm ²		C4
-	-	.027±.001[0.69±0.03mm]			30AWG or 0.05mm ²		C6
-	-	CRIMP	SIZE		TYPE	RANGE	
-	-		WIRE				
-	-	.054 [1.37mm]		F	30-22AWG[0.05-0.35mm ²]		
-	-	INSUL		F	ø.043-.062[1.09-1.57mm]		
WIRE STRIP LENGTH 100-125 [2.54-3.18mm]	TERM APPL SPEC NONE	FEED 900 [5.08mm]	APPLICATOR INSTRUCTIONS 408-8040			SET UP GAGE 458637-1	

TERMINAL NAME: KK® Crimp Terminal							
TE P/N		MOLEX P/N		MOLEX TERMINAL - MOLEX CRIMP SPECS			
1949741-1		08-70-0048					
1949741-2		08-70-0064					
		CRIMP HEIGHT			WIRE SIZE		REF SETTING
-		.032±.001[0.81±0.03mm]			22AWG or 0.35mm ²		B8
-		.030±.001[0.76±0.03mm]			24AWG or 0.20mm ²		C2
-		.028±.001[0.71±0.03mm]			26AWG or 0.12mm ²		C4
-		.027±.001[0.69±0.03mm]			28AWG or 0.08mm ²		C6
-		CRIMP		SIZE	TYPE	RANGE	
-		WIRE		.054 [1.37mm]	F	28-22AWG[0.08-0.35mm ²]	
-		INSUL		.077 [1.96mm]	F	Ø.047-.067[1.20-1.70mm]	
WIRE STRIP LENGTH 1.00 - .125 (2.54-3.18mm)		TERM APPL SPEC NONE		FEED 900 (5.08mm)		APPLICATOR INSTRUCTIONS 408-8040	
						SET UP PAGE 458637-1	

TERMINAL NAME: KK® Crimp Terminal								
TE P/N		MOLEX P/N		MOLEX TERMINAL - MOLEX CRIMP SPECS				
286698-4		08-52-0101						
286698-5		08-65-0815		CRIMP HEIGHT			WIRE SIZE	
286698-6		08-65-0813		.032±.001[0.81±0.03mm]			22AWG or 0.35mm ²	
286698-9		08-70-0046		.030±.001[0.76±0.03mm]			24AWG or 0.20mm ²	
1-286698-0		08-52-0118		.028±.001[0.71±0.03mm]			26AWG or 0.12mm ²	
1-286698-1		08-52-0121		.027±.001[0.69±0.03mm]			28AWG or 0.08mm ²	
1-286698-2		08-50-0321		.0255±.0005[0.645±0.015]			30AWG or 0.05mm ²	
1-286698-3		08-65-0804		CRIMP		SIZE	TYPE	RANGE
1-286698-4		08-65-0801						
1-286698-5		08-65-0811		WIRE		.054 [1.37mm]	F	30-22AWG[0.05-0.35mm ²]
1-286698-6		08-65-0817		INSUL		.077 [1.96mm]	F	Ø.043-.062[1.09-1.57mm]
1-286698-7		40-07-0815						
1-286698-8		97-00-0920						
WIRE STRIP LENGTH 1.00 - .125 [2.54-3.18mm]		TERM APPL SPEC NONE		FEED .900 [22.86mm]		APPLICATOR INSTRUCTIONS 408-8040		SET UP GAGE 458637-1

TERMINAL NAME: KK® Crimp Terminal							
TE P/N		MOLEX P/N		MOLEX TERMINAL - MOLEX CRIMP SPECS			
28698-7		97-00-0444					
-	-	CRIMP HEIGHT			WIRE SIZE		REF SETTING
-	-	.032±.001[0.81±0.03mm]			22AWG or 0.35mm ²		B8
-	-	.030±.001[0.76±0.03mm]			24AWG or 0.20mm ²		C2
-	-	.028±.001[0.71±0.03mm]			26AWG or 0.12mm ²		C4
-	-	.027±.001[0.69±0.03mm]			28AWG or 0.08mm ²		C6
-	-	.0255±.0005[0.645±0.015]			30AWG or 0.05mm ²		C9
-	-	CRIMP		SIZE	TYPE	RANGE	
-	-	WIRE		.054 [1.37mm]	F	30-22AWG[0.05-0.35mm ²]	
-	-	INSUL		.077 [1.96mm]	F	ø .043-.062[1.09-1.57mm]	
WIRE STRIP LENGTH 1.00 - .125 [2.54 - 3.18mm]		TERM APPL SPEC NONE		FEED 900 [5.08mm]			APPLICATOR INSTRUCTIONS 408-8040
							SET UP GAGE 458637-1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR THE ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTRACTING MANUFACTURING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN R. KNEPPER 02JUL2007 CHN T. ELBIN 16JAN2008		 TE Connectivity Harrisburg, PA 17105-3608	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
INCHES		0 PLC $\pm .01$ 1 PLC ± 0.1 2 PLC ± 0.01 3 PLC ± 0.001 4 PLC ± 0.0001 ANGLES $\pm .01$		APVD N. DEMING 16JAN2008 PRODUCT SPEC - APPLICATION SPEC -	
				FINE ADJUST SIDE FEED HDM APPLICATOR -	
MATERIAL		FINISH		SIZE	RESTRICTED TO
				CAGE CODE 00779 DRAWING NO C=1855289	-
CUSTOMER DRAWING				SCALE	REV
				3:5	2 OF 2