



DRAWING MADE IN THIRD ANGLE PROJECTION




© COPYRIGHT 1976 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.



DETAIL ID



SECTION A-A
NOT TO SCALE



SECTION B-B
NOT TO SCALE

△ .000030 MIN. GOLD OVER .000050 NICKEL.

REVISIONS						
P	H	ZONE	LTR	DESCRIPTION	DATE	APPROVED
✓	✓		E	REDRAWN W/O CHANGE M-6457	6-5-81	MSF/SH
✓			F	REVISED AG 57	10/21/83	SP W. R. S. J. J. J.
✓			G	ADDED -6 PER TTI CM 84-03	9-27-81	KW 1/28
✓			G1	RESTORATION	4-23-85	ST 1/83
✓			H	OBSOLETE -6 PER CM-2604	11-2-89	PKC RS
✓			J	REVISED PER CM-2812	3-26-90	PKC RS
			K	REACT. -6 PER PR CM 91-144	12-17-91	DS RS
			L	REV PER EC 0730-3607-91	1-6-94	RV RS

△	.012 PH BRZ	350925-6
PRE-TIN	.012 BRASS	350925-1
FINISH	MATERIAL	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.015 ANGLES ±	CONTRACT NO DR m. Fehrer 4-21-81 CHK D. S. Weide 6/9/81 APPD R. Polakof 6-10-81 APPD DSGN APPD OTHER APPD	AMP AMP INCORPORATED Harrisburg, Pa.
WIRE RANGE 30-26 AWG	NAME SOCKET, UNIVERSAL MATE-N-LOK	SIZE B
INSULATION RANGE .032-.057 DIA	CODE IDENT NO 00779	DRAWING NO 350925
	SCALE 4-1	SHEET