

AHC ATTENUATORS

SMA, 6 GHz, 2 Watts

SPECIFICATIONS:

Models: AHC

RoHS
Compliant

AEROFLEX
A passion for performance.

Electrical:

Frequency Range _____ DC - 6.0 GHz

Standard dB Values _____ 0 - 10, 12, 15, 20, 30 & 40 dB

Attenuation Accuracy:

0 - 10 dB _____ ± 0.5 dB

12, 15, 20 dB _____ ± 0.7 dB

30 dB _____ ± 0.9 dB

40 dB _____ ± 1.5 dB

VSWR _____ 1.20:1 Max.

Input Power _____ 2 Watts Avg. @ 25°C

Derated Linearly to 1.1 Watts at +85°C

Impedance _____ 50 Ohms


Operating Temp Range _____ -20°C to +85°C

Mechanical:


SMA Connectors _____ Passivated Stainless Steel

Mates with MIL-STD-348

Conductors _____ Gold Plated Beryllium Copper



0-12, 15 & 20dB



30 & 40dB

HOW TO ORDER:

Model Number: AHC-XX

dB Value

Ordering Examples:

Model Number: AHC-3

DC - 6 GHz; 3 dB; SMA - Male/Fem

Model Number: AHC-10

DC - 6 GHz; 10 dB; SMA - Male/Fem

Note: Dimensions in Brackets are Expressed in Millimeters and are for Reference Only.
Design specifications are subject to change without notice.
Contact factory for technical specifications before purchasing or use.

AHC-ATT: REV E

AEROFLEX
INMET

Aeroflex / Inmet, Inc. • 300 Dino Drive, Ann Arbor, MI 48103 • U.S.A.
888-244-6638 or 734-426-5553 • FAX: 734-426-5557
www.aeroflex.com/inmet • inmet-sales@eroflex.com