




Spectra Low Profile Edge Mount 015 & 017





-  From only 3mm high.
-  Up to 2 changeover or ON/OFF contacts.
-  Front marking and easy to operate sliders.
-  Patented 1 micron hard gold plated contacts.



PCB drilling matrix




Changeover Contacts


Dual in line
(centre common pin)Single in line
(centre common pin)

On/Off Contacts

Single in line



Single in line



Principal Electrical and Performance Data

at 20°C 70% R.H.

Contact Ratings: Non Switching: 100Vac, 5A.
Switching: 1 μ V to 100V, 1 μ A to 1, 10A.

Initial Contact Resistance: (at 10mV, 10mA max).
Typical: 10m Ω .

Insulation Resistance: (at 500 Vdc min.) 10,000M Ω .

Life: Mechanical wear out of the sliding actuator is usually
observed after 10,000 operations.

Dielectric Strength: 1 minute: 500Vrms 50Hz.

Capacitance Between Open Contacts: < 1pF at 1KHz.

Temperature: Operating range for continuous electrical use
and manual operation is restricted to 55°C to +85°C for standard
products.

Operating Force per pole: Typical: 4N.

Humidity: BS 2011 Test Ca: 56 days.

Solderability: < 2 seconds to wet at 235°C as per IEC 68 and
BS 2011 Test T, solder bath method. We recommend that these
switches are post fitted after PCB cleaning has been carried out.

Resistance to soldering heat as per IEC 68 and BS 2011 10
seconds satisfactory at 260°C when mounted on 1.5mm PCB.

ITW Erg Components

Luton Road, Dunstable, Bedfordshire LU5 4LJ England
Telephone: 01582 662241 Fax: 01582 600767

E-mail: info@erg.co.uk <http://www.erg.co.uk>

This leaflet is believed to contain the best information available at the time of printing, but is
subject to change without notice. Performance figures, where quoted, are actually estimates
based on our experience or that of our customers or statutory authorities. In common with all
components reliability varies with many factors, and users are invited to contact us in
appropriate cases so that where relevant information is available it may be considered by the
user. All supplies are subject to the Company's standard conditions of sale which are available
on request.