



UL


Headers

to Type 251

 **Type 235** page 145

 **Type 236** page 149

Accessories

for Type 251

coding set

700025 page 206

Type 251

Screw type terminal block, pluggable, centerline 5.08 mm / 0.200 inches, wire entry parallel to plug direction, lift system, contact system with integrated wire protection, with mounting flange

Technical Data

UL V / A / AWG 300 / 16 / 28 - 12

 0.08 - 2.5 mm² 250 V / 4 kV / 12 A

Insulation co-ordination according to EN 60664-1

Clearance and creepage distances min. 3.6 mm

Insulating material class CTI 600

Overvoltage category III III II

Pollution degree 3 2 2

Rated voltage 250 630 630

Rated test voltage 2.5 6 4

Protection category according to IEC 529 IP20

Tightening torque UL 4.4 lb-in max.


Min. insul. strip length 8 mm

Pole size 2 - 24

Color black

Dimensions in mm

1 mm = 0.0394 in.



Part numbers (P/N)

(information: page 56)

Complete the part number by adding the pole size.

Type 251

centerline 5.08 mm / 0.200 inches

P/N 312511

	02	03	04	05	06	07	08
09	10	11	12	13	14	15	16
17	18	19	20	21	22	23	24

Type 251

centerline 10.16 mm / 0.400 inches

P/N 312512

	02	03	04	05	06	07	08
09	10	11	12				

 Standard pole sizes

 Available on demand. Minimum order quantity 5000 pieces per item.