



DO NOT
SCALE FROM
THIS PRINTFIG 1
IPL1-106-01-XXX-D-P SHOWN

NOTES:

1. \odot REPRESENTS A CRITICAL DIMENSION.
2. NOTE DELETED.
3. MINIMUM TERMINAL RETENTION: 1 LB.
4. PARTS TO BE MOLDED TO POSITION.
5. POST MUST BE WITHIN .005 [1.3] OF EACH OTHER.
6. ALL PIN TO PIN DIMENSIONS TO BE MEASURED FROM TIP TO TIP.
7. NOTE DELETED.
8. DIMENSION TO BE MEASURED AT BEND.
9. TIP TO BE FLUSH TO .015 BELOW TOP OF SHROUD.
10. BOTH ROWS TO BE SYMMETRIC WITHIN .010 [0.25].
11. THIS NUMBER REPRESENTS THE NUMBER OF POSITIONS PER ROW ONLY AND IS NOT INTENDED TO BE USED IN POSITION NUMBERING.
12. 1 OR 2 GATE PADS TO BE PRESENT AT VENDOR DISCRETION.

IPL1-1XX-XX-XXX-D-XX-X

No OF POSITIONS
-02 THRU -25
(PER ROW)

LEAD STYLE

-01: THROUGH HOLE
(USE T-1S64-XX-XX)
-02: SURFACE MOUNT
(SEE FIG 2, SHT 2)
(USE T-1S64-XX-XX)

OPTION

-P: POLARIZATION (SEE FIG 1)
(USE IPL1-XX-D-P)
(NOT AVAILABLE W/ -K OR -G, OPTIONS)
-K: KEYED POLARIZATION
(USE IPL1-XX-D-K)
(SEE FIG 5, SHEET 3)
(NOT AVAILABLE W/ -P OR -G, OPTIONS)
-G: GUIDE POSTS (SEE FIG 6 & 7, SHEET 3)
(USE IPL1-XX-D-GP)
(NOT AVAILABLE W/ -P, -K OPTIONS)
(LEAVE BLANK FOR NO POLARIZATION
(SEE FIG 4, SHEET 3), SAMTEC WILL ONLY SUPPORT
EXISTING BUSINESS AS OF REV U)

OPTION



-RA: RIGHT ANGLE (SEE FIG 3, SHT 2)
(AVAILABLE WITH -01 LEAD STYLE ONLY)

ROW SPECIFICATION

-D: DOUBLE (USE IPL1-XX-D)

PLATING SPECIFICATION

-F: FLASH SELECTIVE (USE T-1S64-XX-F)
-L: LIGHT SELECTIVE (USE T-1S64-XX-L)
-S: SELECTIVE (USE T-1S64-XX-S)
-H: HEAVY GOLD (T-1S64-XX-H)
-FM: FLASH SELECTIVE/MATTE TIN TAILS (USE T-1S64-XX-F)
-LM: LIGHT SELECTIVE/MATTE TIN TAILS (USE T-1S64-XX-L)
-SM: SELECTIVE/MATTE TIN TAILS (USE T-1S64-XX-S)
-STL: SELECTIVE/ TIN/LEAD TAILS (USE T-1S64-XX-STL)



SECTION "A"-A"

SECTION "A"-A"

SECTION "A"-A"

SECTION "A"-A"

SECTION "A"-A"

LEAD STYLE	OPTION	TERMINAL 1	OAL REF	TERMINAL 2	OAL REF
-01	NONE	T-1S64-07-X	.430 [10.92]	N/A	N/A
-01	-RA	T-1S64-09-X	.530 [13.46]	T-1S64-10-X	.730 [18.54]
-02	NONE	T-1S64-08-X	.445 [11.30]	N/A	N/A

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.
TOLERANCES ARE:
DECIMALS ANGLES
.XX: $\pm .01$ [0.3] $\pm 2^\circ$
.XXX: $\pm .005$ [0.13] $\pm .0005$ [0.013]
.XXXX: $\pm .0020$ [0.051]

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
THAT IS THE PROPERTY OF SAMTEC INC.
AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC INC.

samtec
520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

MATERIAL: DO NOT SCALE DRAWING
SHEET SCALE: 3:1
INSULATOR: LCP UL94-V0, COLOR: BLACK
-K INSULATOR: LCP UL94-V0, COLOR: NATURAL
TERMINAL: PHOS BRONZE

DESCRIPTION:
.100 [2.54] DOUBLE ROW TERMINAL ASSEMBLY
DWG. NO.
IPL1-1XX-XX-XXX-D-XX-X
BY: KEVIN B 03/11/02 SHEET 1 OF 3

FIG 2
IPL1-106-02-XXX-D-P SHOWN
[DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1]






TABLE 2	
No OF POS.	COPLANARITY
-02 THRU -05	.004 [.10]
-06 THRU -10	.005 [.13]
-11 THRU -25	.006 [.15]

-02: SURFACE MOUNT INPROCESS 1




-02: SURFACE MOUNT INPROCESS 2



PACKAGING VIEWS

(ASSEMBLIES TO HAVE POSITION #1 LOADED IN THE SAME DIRECTION AS ARROW ON TUBE, EXCEPT WITH -RA OPTION)



PACKAGING TABLE

LEAD STYLE	OPTION	PACKAGING TUBE	PLUG
-01	NONE	PT-1-24-15-29	TP-07
-01 (2 POSITION)	NONE	PT-TSM004-DV	TP-07
-01	-RA	PT-1-24-04-40	TP-07
-02	NONE	PT-1-24-02-08	TP-13





FIG 3
IPL1-106-01-XXX-D-RA-P SHOWN
[DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1]



SECTION "B"- "B"

F:\DWG\MISC\MKT\IPL1-1XX-XX-XXX-D-XX-X-MKT.SLDDRW

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

samtec
520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322


DESCRIPTION: .100[2.54] DOUBLE ROW TERMINAL ASSEMBLY

DWG. NO. IPL1-1XX-XX-XXX-D-XX-X


BY: KEVIN B 03/11/02 SHEET 2 OF 3

REVISION AF


-RA: INPROCESS 1



-RA: INPROCESS 2




-RA: INPROCESS 3



C12

SEE NOTE 9



-RA: INPROCESS 4

FIG 4
(IPL1-106-01-XXX-D SHOWN)
(DIFFERENT AS SHOWN,
OTHERWISE SAME AS FIG 1)

SAMTEC WILL ONLY SUPPORT
EXISTING BUSINESS AS OF REV. U





FIG 5
(IPL1-106-01-XXX-D-K SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 4)





FIG 6
(IPL1-106-01-XXX-D-G SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 3)









FIG 7
(IPL1-102-01-XXX-D-G SHOWN)
(DIFFERENT AS SHOWN,
OTHERWISE SAME AS FIG 1)



PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1