


# MC10195

## Hex Inverter/Buffer

The MC10195 is a Hex Buffer Inverter which is built using six EXCLUSIVE NOR gates. There is a common input to these gates which when placed low or left open allows them to act as inverters. With the common input connected to a high logic level the MC10195 is a hex buffer, useful for high fanout clock driving and reducing stub lengths on long bus lines.

- $P_D = 200 \text{ mW typ/pkg (No Load)}$
- $t_{pd} = 2.8 \text{ ns typ (B-Q)}$
- $t_{pd} = 3.8 \text{ ns typ (A-Q)}$
- $t_r, t_f = 2.5 \text{ ns typ (20\%–80\%)}$



**TRUTH TABLE**


| Inputs |   | Output |
|--------|---|--------|
| A      | B | Q      |
| L      | L | H      |
| L      | H | L      |
| H      | L | L      |
| H      | H | H      |





**ON Semiconductor**

<http://onsemi.com>


### MARKING DIAGRAMS




**CDIP-16**  
**L SUFFIX**  
**CASE 620**



**PDIP-16**  
**P SUFFIX**  
**CASE 648**




**PLCC-20**  
**FN SUFFIX**  
**CASE 775**



A = Assembly Location  
WL = Wafer Lot  
YY = Year  
WW = Work Week

### DIP PIN ASSIGNMENT



Pin assignment is for Dual-in-Line Package.  
For PLCC pin assignment, see the Pin Conversion Tables on page 18 of the ON Semiconductor MECL Data Book (DL122/D).

### ORDERING INFORMATION

| Device    | Package | Shipping        |
|-----------|---------|-----------------|
| MC10195L  | CDIP-16 | 25 Units / Rail |
| MC10195P  | PDIP-16 | 25 Units / Rail |
| MC10195FN | PLCC-20 | 46 Units / Rail |

## ELECTRICAL CHARACTERISTICS

| Characteristic                   | Symbol              | Pin Under Test | Test Limits |            |        |     |            |        |            | Unit |
|----------------------------------|---------------------|----------------|-------------|------------|--------|-----|------------|--------|------------|------|
|                                  |                     |                | −30°C       |            | +25°C  |     |            | +85°C  |            |      |
|                                  |                     |                | Min         | Max        | Min    | Typ | Max        | Min    | Max        |      |
| Power Supply Drain Current       | I <sub>E</sub>      | 8              |             | 54         |        | 39  | 49         |        | 54         | mAdc |
| Input Current                    | I <sub>inH</sub>    | 5<br>9         |             | 425<br>460 |        |     | 265<br>290 |        | 265<br>290 | μAdc |
|                                  | I <sub>inL</sub>    | 5              | 0.5         |            | 0.5    |     |            | 0.3    |            | μAdc |
| Output Voltage      Logic 1      | V <sub>OH</sub>     | 2              | −1.060      | −0.890     | −0.960 |     | −0.810     | −0.890 | −0.700     | Vdc  |
| Output Voltage      Logic 0      | V <sub>OL</sub>     | 2              | −1.890      | −1.675     | −1.850 |     | −1.650     | −1.825 | −1.615     | Vdc  |
| Threshold Voltage    Logic 1     | V <sub>OHA</sub>    | 2              | −1.080      |            | −0.980 |     |            | −0.910 |            | Vdc  |
| Threshold Voltage    Logic 0     | V <sub>OLA</sub>    | 2              |             | −1.655     |        |     | −1.630     |        | −1.595     | Vdc  |
| Switching Times (50Ω Load)       |                     |                |             |            |        |     |            |        |            | ns   |
| Propagation Delay                | t <sub>5+2−</sub>   | 2              | 1.1         | 4.2        | 1.1    | 2.8 | 4.0        | 1.1    | 4.4        |      |
|                                  | t <sub>7−4+</sub>   | 4              | 1.1         | 4.2        | 1.1    | 2.8 | 4.0        | 1.1    | 4.4        |      |
|                                  | t <sub>10+13+</sub> | 13             | 1.1         | 4.2        | 1.1    | 2.8 | 4.0        | 1.1    | 4.4        |      |
|                                  | t <sub>11−14−</sub> | 14             | 1.1         | 4.2        | 1.1    | 2.8 | 4.0        | 1.1    | 4.4        |      |
|                                  | t <sub>9−14−</sub>  | 14             | 1.1         | 5.2        | 1.1    | 3.8 | 5.0        | 1.1    | 5.4        |      |
| Rise Time            (20 to 80%) | t <sub>2+</sub>     | 2              | 1.1         | 4.7        | 1.1    | 2.5 | 4.5        | 1.1    | 5.0        |      |
| Fall Time            (20 to 80%) | t <sub>2−</sub>     | 2              | 1.1         | 4.7        | 1.1    | 2.5 | 4.5        | 1.1    | 5.0        |      |

## ELECTRICAL CHARACTERISTICS (continued)


| @ Test Temperature         |                     |                | TEST VOLTAGE VALUES (Volts)               |                    |                     |                    |                 | (V <sub>CC</sub> )<br>Gnd |
|----------------------------|---------------------|----------------|-------------------------------------------|--------------------|---------------------|--------------------|-----------------|---------------------------|
|                            |                     |                | V <sub>IHmax</sub>                        | V <sub>ILmin</sub> | V <sub>IHAmin</sub> | V <sub>ILAmx</sub> | V <sub>EE</sub> |                           |
|                            |                     |                | -30°C                                     | -0.890             | -1.890              | -1.205             | -1.500          | -5.2                      |
|                            |                     |                | +25°C                                     | -0.810             | -1.850              | -1.105             | -1.475          | -5.2                      |
|                            |                     |                | +85°C                                     | -0.700             | -1.825              | -1.035             | -1.440          | -5.2                      |
| Characteristic             | Symbol              | Pin Under Test | TEST VOLTAGE APPLIED TO PINS LISTED BELOW |                    |                     |                    |                 | (V <sub>CC</sub> )<br>Gnd |
|                            |                     |                | V <sub>IHmax</sub>                        | V <sub>ILmin</sub> | V <sub>IHAmin</sub> | V <sub>ILAmx</sub> | V <sub>EE</sub> |                           |
| Power Supply Drain Current | I <sub>E</sub>      | 8              |                                           |                    |                     |                    | 8               | 1, 16                     |
| Input Current              | I <sub>inH</sub>    | 5<br>9         | 5<br>9                                    |                    |                     |                    | 8<br>8          | 1, 16<br>1, 16            |
|                            | I <sub>inL</sub>    | 5              |                                           | 5                  |                     |                    | 8               | 1, 16                     |
| Output Voltage Logic 1     | V <sub>OH</sub>     | 2              |                                           |                    |                     |                    | 8               | 1, 16                     |
| Output Voltage Logic 0     | V <sub>OL</sub>     | 2              | 9                                         |                    |                     |                    | 8               | 1, 16                     |
| Threshold Voltage Logic 1  | V <sub>OHA</sub>    | 2              |                                           |                    |                     | 5                  | 8               | 1, 16                     |
| Threshold Voltage Logic 0  | V <sub>OLA</sub>    | 2              |                                           |                    | 5                   |                    | 8               | 1, 16                     |
| Switching Times (50Ω Load) |                     |                |                                           |                    | Pulse In            | Pulse Out          | -3.2 V          | +2.0 V                    |
| Propagation Delay          | t <sub>5+2-</sub>   | 2              |                                           |                    | 5                   | 2                  | 8               | 1, 16                     |
|                            | t <sub>7-4+</sub>   | 4              |                                           |                    | 7                   | 4                  | 8               | 1, 16                     |
|                            | t <sub>10+13+</sub> | 13             |                                           |                    | 10                  | 13                 | 8               | 1, 16                     |
|                            | t <sub>11-14-</sub> | 14             |                                           |                    | 11                  | 14                 | 8               | 1, 16                     |
|                            | t <sub>9-14-</sub>  | 14             |                                           |                    | 9                   | 14                 | 8               | 1, 16                     |
| Rise Time (20 to 80%)      | t <sub>2+</sub>     | 2              |                                           |                    | 5                   | 2                  | 8               | 1, 16                     |
| Fall Time (20 to 80%)      | t <sub>2-</sub>     | 2              |                                           |                    | 5                   | 2                  | 8               | 1, 16                     |

Each MECL 10,000 series circuit has been designed to meet the dc specifications shown in the test table, after thermal equilibrium has been established. The circuit is in a test socket or mounted on a printed circuit board and transverse air flow greater than 500 linear fpm is maintained. Outputs are terminated through a 50-ohm resistor to -2.0 volts. Test procedures are shown for only one gate. The other gates are tested in the same manner.

# MC10195

## PACKAGE DIMENSIONS

PLCC-20  
FN SUFFIX  
PLASTIC PLCC PACKAGE  
CASE 775-02  
ISSUE C




### NOTES:

1. DATUMS -L-, -M-, AND -N- DETERMINED WHERE TOP OF LEAD SHOULDER EXITS PLASTIC BODY AT MOLD PARTING LINE.
2. DIMENSION G1, TRUE POSITION TO BE MEASURED AT DATUM -T-, SEATING PLANE.
3. DIMENSIONS R AND U DO NOT INCLUDE MOLD FLASH. ALLOWABLE MOLD FLASH IS 0.010 (0.250) PER SIDE.
4. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
5. CONTROLLING DIMENSION: INCH.
6. THE PACKAGE TOP MAY BE SMALLER THAN THE PACKAGE BOTTOM BY UP TO 0.012 (0.300). DIMENSIONS R AND U ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY EXCLUSIVE OF MOLD FLASH, TIE BAR BURRS, GATE BURRS AND INTERLEAD FLASH, BUT INCLUDING ANY MISMATCH BETWEEN THE TOP AND BOTTOM OF THE PLASTIC BODY.
7. DIMENSION H DOES NOT INCLUDE DAMBAR PROTRUSION OR INTRUSION. THE DAMBAR PROTRUSION(S) SHALL NOT CAUSE THE H DIMENSION TO BE GREATER THAN 0.037 (0.940). THE DAMBAR INTRUSION(S) SHALL NOT CAUSE THE H DIMENSION TO BE SMALLER THAN 0.025 (0.635).

| DIM | INCHES    |       | MILLIMETERS |       |
|-----|-----------|-------|-------------|-------|
|     | MIN       | MAX   | MIN         | MAX   |
| A   | 0.385     | 0.395 | 9.78        | 10.03 |
| B   | 0.385     | 0.395 | 9.78        | 10.03 |
| C   | 0.165     | 0.180 | 4.20        | 4.57  |
| E   | 0.090     | 0.110 | 2.29        | 2.79  |
| F   | 0.013     | 0.019 | 0.33        | 0.48  |
| G   | 0.050 BSC |       | 1.27 BSC    |       |
| H   | 0.026     | 0.032 | 0.66        | 0.81  |
| J   | 0.020     | —     | 0.51        | —     |
| K   | 0.025     | —     | 0.64        | —     |
| R   | 0.350     | 0.356 | 8.89        | 9.04  |
| U   | 0.350     | 0.356 | 8.89        | 9.04  |
| V   | 0.042     | 0.048 | 1.07        | 1.21  |
| W   | 0.042     | 0.048 | 1.07        | 1.21  |
| X   | 0.042     | 0.056 | 1.07        | 1.42  |
| Y   | —         | 0.020 | —           | 0.50  |
| Z   | 2°        | 10°   | 2°          | 10°   |
| G1  | 0.310     | 0.330 | 7.88        | 8.38  |
| K1  | 0.040     | —     | 1.02        | —     |

# MC10195


## CDIP-16 L SUFFIX CERAMIC DIP PACKAGE CASE 620-10 ISSUE T



- NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
  2. CONTROLLING DIMENSION: INCH.
  3. DIMENSION L TO CENTER OF LEAD WHEN FORMED PARALLEL.
  4. DIMENSION F MAY NARROW TO 0.76 (0.030) WHERE THE LEAD ENTERS THE CERAMIC BODY.

|     | INCHES    |       | MILLIMETERS |       |
|-----|-----------|-------|-------------|-------|
| DIM | MIN       | MAX   | MIN         | MAX   |
| A   | 0.750     | 0.785 | 19.05       | 19.93 |
| B   | 0.240     | 0.295 | 6.10        | 7.49  |
| C   | —         | 0.200 | —           | 5.08  |
| D   | 0.015     | 0.020 | 0.39        | 0.50  |
| E   | 0.050 BSC |       | 1.27 BSC    |       |
| F   | 0.055     | 0.065 | 1.40        | 1.65  |
| G   | 0.100 BSC |       | 2.54 BSC    |       |
| H   | 0.008     | 0.015 | 0.21        | 0.38  |
| K   | 0.125     | 0.170 | 3.18        | 4.31  |
| L   | 0.300 BSC |       | 7.62 BSC    |       |
| M   | 0°        | 15°   | 0°          | 15°   |
| N   | 0.020     | 0.040 | 0.51        | 1.01  |

## PDIP-16 P SUFFIX PLASTIC DIP PACKAGE CASE 648-08 ISSUE R



- NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
  2. CONTROLLING DIMENSION: INCH.
  3. DIMENSION L TO CENTER OF LEADS WHEN FORMED PARALLEL.
  4. DIMENSION B DOES NOT INCLUDE MOLD FLASH.
  5. ROUNDED CORNERS OPTIONAL.

|     | INCHES    |       | MILLIMETERS |       |
|-----|-----------|-------|-------------|-------|
| DIM | MIN       | MAX   | MIN         | MAX   |
| A   | 0.740     | 0.770 | 18.80       | 19.55 |
| B   | 0.250     | 0.270 | 6.35        | 6.85  |
| C   | 0.145     | 0.175 | 3.69        | 4.44  |
| D   | 0.015     | 0.021 | 0.39        | 0.53  |
| F   | 0.040     | 0.70  | 1.02        | 1.77  |
| G   | 0.100 BSC |       | 2.54 BSC    |       |
| H   | 0.050 BSC |       | 1.27 BSC    |       |
| J   | 0.008     | 0.015 | 0.21        | 0.38  |
| K   | 0.110     | 0.130 | 2.80        | 3.30  |
| L   | 0.295     | 0.305 | 7.50        | 7.74  |
| M   | 0°        | 10°   | 0°          | 10°   |
| S   | 0.020     | 0.040 | 0.51        | 1.01  |

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer.

## PUBLICATION ORDERING INFORMATION

### North America Literature Fulfillment:

Literature Distribution Center for ON Semiconductor  
P.O. Box 5163, Denver, Colorado 80217 USA  
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
Email: ONlit@hibbertco.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

### EUROPE: LDC for ON Semiconductor – European Support

German Phone: (+1) 303-308-7140 (M-F 2:30pm to 5:00pm Munich Time)  
Email: ONlit-german@hibbertco.com  
French Phone: (+1) 303-308-7141 (M-F 2:30pm to 5:00pm Toulouse Time)  
Email: ONlit-french@hibbertco.com  
English Phone: (+1) 303-308-7142 (M-F 1:30pm to 5:00pm UK Time)  
Email: ONlit@hibbertco.com

### ASIA/PACIFIC: LDC for ON Semiconductor – Asia Support

Phone: 303-675-2121 (Tue-Fri 9:00am to 1:00pm, Hong Kong Time)  
Toll Free from Hong Kong 800-4422-3781  
Email: ONlit-asia@hibbertco.com

### JAPAN: ON Semiconductor, Japan Customer Focus Center

4-32-1 Nishi-Gotanda, Shinagawa-ku, Tokyo, Japan 141-8549  
Phone: 81-3-5740-2745  
Email: r14525@onsemi.com

Fax Response Line: 303-675-2167

800-344-3810 Toll Free USA/Canada

ON Semiconductor Website: <http://onsemi.com>

For additional information, please contact your local Sales Representative.