





Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de © FCI. Droits de reproduction FCI.





RECOMMENDED PCB LAYOUT  
(ALL TOLERANCES ARE  $\pm 0.05$ )

SCALE 3:1

1. MATERIAL:  
CONTACT: HIGH TEMPERATURE PLASTIC, UL94V-0  
CONTACT: COPPER ALLOY  
HOLD DOWN: COPPER ALLOY
2. FINISH:  
CONTACT: 1,27 $\mu$ m MIN NICKEL UNDERPLATE OVERALL,  
2,54 $\mu$ m MIN TIN (LEAD-FREE) ON SOLDER TAIL,  
0,76 $\mu$ m MIN GOLD IN CONTACT AREA
3. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY  
REGULATIONS AS DESCRIBED IN GS-22-008
4. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE  
FOR 10 SECONDS IN A CONVECTION, INFRARED OR VAPOR PHASE REFLOW OVEN
5. CONTACT WIPE: 2.07 MIN FUR SIGNAL AND 2.52 MIN FUR GROUND

|                         |                |          |
|-------------------------|----------------|----------|
| 4 LANE R/A<br>TH HEADER | no<br>10035104 | Rev<br>B |
| title                   | CUSTOMER       |          |
| catlog no               | sheet 2 of 2   |          |