

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

—

© COPYRIGHT

By

ALL RIGHTS RESERVED

| |
|-----|
| LOC |
| CM |

| |
|-----|
| LOC |
|-----|

| | |
|------|----|
| DIST | 54 |
|------|----|

| | |
|------|--|
| DIST | |
|------|--|

REVISIONS

P

LTR

DESCRIPTION

DATE _____

| |
|-----|
| DWN |
|-----|

APV

3

RE

1552

PER





ECO:

- 12 -

050CT

| |
|----|
| KH |
|----|

SM



| | | | |
|------|------|------|-------|
| .065 | 1.65 | | |
| .063 | 1.60 | .936 | 23.77 |
| .060 | 1.52 | .850 | 16.51 |
| .045 | 1.14 | .500 | 12.70 |
| .030 | 0.76 | .450 | 11.43 |
| .015 | 0.38 | .425 | 10.80 |
| .012 | 0.30 | .300 | 7.62 |
| .010 | 0.25 | .180 | 4.57 |
| .009 | 0.23 | .157 | 3.99 |
| .008 | 0.20 | .156 | 3.96 |
| .005 | 0.13 | .125 | 3.18 |
| .003 | 0.08 | .078 | 1.98 |
| .001 | 0.03 | .073 | 1.85 |
| .000 | 0.00 | .070 | 1.78 |
| IN | MM | IN | MM |

CONVERSION TABLE





647268-6 SHOWN

| | |
|---------------------|-------------|
| 6 | 647268-6 |
| 4 | 647268-4 |
| NUMBER OF POSITIONS | PART NUMBER |

55



TE Connectivity

| | | | | |
|---|--|---|---|---------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DIN 16JUL98 B. LEWIS CHK 16JUL98 R. SWING |  TE Connectivity | |
| DIMENSIONS: INCHES | TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± .— 1 PLC ± .— 2 PLC ± .— 3 PLC ± .005 4 PLCS ± .— ANGLES ± .— | APVD 16JUL98 C. JONES PRODUCT SPEC — APPLICATION SPEC — | NAME MTA-156 HEADER ASSEMBLY, FRICTION LOCK, RIGHT ANGLE, REAR BEND, .045 SQUARE POST, TIN PLATED, SPECIAL | |
|  | | | SIZE A1 | CASE CODE 00779 |
| MATERIAL  | FINISH  | WEIGHT — | DRAWING NO 6-47268 | RESTRICTED — |
| CUSTOMER DRAWING | | | SCALE 5:1 | SHEET 1 OF 1 |
| | | | REV 1 | |